





- 1.0 GENERAL NOTES
- 1.1 ALL METRIC DIMENSIONS ARE IN BRACKETS [X. X]
- 1.2 MARK PART WITH IDENTIFICATION NUMBER.
- 2.0 DESIGN NOTES
- 2.1 DESIGNED PER CUSTOMER REQUIREMENTS.
- 3.0 MANUFACTURING/SPECIAL REQUIREMENTS
- 3.1 TIGHTEN ALL BOLTS SECURING FLAT PLATES BY THE TURN-OF-NUT METHOD. TIGHTEN ALL U-BOLTS USING TURN-OF-NUT METHOD WITH ATTENTION TO LEAVE EQUAL DISTANCE AND EQUAL FORCE ON EACH LEG OF THE U-BOLT.
- 4.0 TEST
- 5.0 PACKAGING
- 5.1 PACKAGING SHALL MEET COMMSCOPE REQUIREMENTS PER DOCUMENT IS-PL-3005
- 5.2 PRINTED DOCUMENT TO BE PLACED INSIDE POLYBAG AND THEN IN SHIPPING CONTAINER
- 5.3 EXTRA HARDWARE MAY BE SUPPLIED, BAGGED AND SHIPPED





PACKAGE



COMPONENT PART NUMBERS PROVIDED FOR ASSEMBLY PURPOSES;
INDIVIDUAL COMPONENTS MAY BE SHIPPED AS PARTS WITHIN AN INCLUDED KIT.

ITEM	PART NO.	DESCRIPTION	QTY.	WEIGHT
1	V-CLAMP	CLAMP, 4 SLOT V	8	4.90 LBS
2	MT-381	5/8" X 12" GALV THREADED ROD	8	1.04 LBS
3	GWFO5A	GALV FLAT WASHER HARDENED 5/8", 1.3OD	32	0.04 LBS
4	GWL-05	5/8" GALV LOCK WASHER	32	0.03 LBS
5	GN-05	5/8" GALV HEX NUT	32	0.08 LBS

DENSITY	MASS	52.21	lbs/in³
VOLUME	184.02		lbs
SURFACE AREA	1165.94		in³
HEIGHT	(12.25[311.2])		
LENGTH	8.38[212.7]		
WIDTH	4.25[108.0]		

COMMSCOPE, INC. OF NORTH CAROLINA																	
TOLERANCES					SAP MATERIAL MASTER												
0 PLACE		X[X] ± 0.25[6.3]		2 PLACE		.XX[X] ± 0.06[1.5]		VZWSMART-MSK3D									
1 PLACE		.X[X] ± 0.12[3.0]		ANGLES		± 2°											
FINISH					MATERIAL												
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES INTERPRET PER ANSI Y 14.5M-1994		NAME		DATE		TITLE CLAMP, PIPE TO PIPE, 1.66" TO 4.50", HD											
	CE	MRC		04/01/20													
	RW	RY1002		03/02/2025													
	AD	YMENG		03/03/2025													
	RE	YMENG		03/19/2025													
	ECN 50101510AMO				SCALE 1:2		DOCUMENT NO. VZWSMART-MSK3D										
SIZE		Auth Group		INSL		MODEL		DRAWING		SHEET 1 OF 1							
C						VERSION 04		STATUS RE			REVISION B		VERSION 06		STATUS RE		REVISION D