HFT206-2SBVSJ-G



HELIAX® Hybrid Cable Assembly, 6-OVP box to RRU, Power Cord to RRU UR Type TC-ER, 2 Power conductors 6 AWG RRU, 6 AWG OVP, 2 fiber Bi-Di Jonhon adapter compatible pvc jacket aluminum armor, OVP gland insert kit included

Jonhon adapter compatible, de-latching component included

Product Classification

Regional Availability North America

Product Type Hybrid cable assembly

Product Brand HELIAX®

Product Series HFT

Ordering Note ANDREW® non-standard product

General Specifications

Conductors, quantity 2

Construction Type Hybrid standard tail

Interface, Connector A LC

Interface Feature, connector A Outdoor
Interface Body Style, connector A Straight

Interface, Connector B LC

Interface Feature, connector BStandardInterface Body Style, connector BStraightJacket ColorBlackTotal Fibers, quantity2

Dimensions

Cable Assembly Length Range (ft) 3 - 50


Diameter Over Jacket 18.31 mm | 0.721 in

Center Conductor Gauge 6 AWG

Ordering Tree



HFT206-2SBVSJ-G



Representative Image



Mechanical Specifications

Minimum Bend Radius 221 mm | 8.701 in

Optical Specifications

Fiber ModeSinglemodeFiber TypeG.657.A2

Insertion Loss, typical note Insertion loss is measured at 1310 and 1550 nm



HFT206-2SBVSJ-G

Insertion Loss, typical

0.5

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+75 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+167 \,^{\circ}\text{F}$)

Packaging and Weights

Cable weight 0.5 kg/m | 0.336 lb/ft

* Footnotes

Insertion Loss, typical note Insertion loss is measured at a room temp of +20°C (+68°F)

