# URGRPRX7R

#### **Base Product**



Ultra Low Loss (ULL) Singlemode G.657.A2 MPO16 (Non-Pinned) to MPO16 (Pinned), Fiber Array Cable Assembly, 16-Fiber, Dual Rated (OFNR /LSZH)

#### Product Classification

Regional Availability	Asia   Australia/New Zealand   China   Europe   India   Latin America   Middle East/Africa   North America
Portfolio	CommScope®
Product Type	Fiber array cable assembly
Product Brand	Propel   SYSTIMAX ULL
Ordering Note	For additional jacket colors, please contact a CommScope Sales Representative   For lengths greater than 999 ft (304 m), orders must be in meters   Minimum length may vary based on cable configuration

#### General Specifications

Cable Assembly Length Range (m)

Connector A, quantity	1
Color, boot A	Black
Color, connector A	Green
Connector B, quantity	1
Color, boot B	Black
Color, connector B	Green
Construction Type	Stranded
Furcation Color	Yellow
Interface, Connector A	MPO-16/APC Female
Interface, Connector B	MPO-16/APC Male
Jacket Color	Yellow
Polarity	Method B Enhanced (ULL)
Fibers per Subunit, quantity	16
Total Fibers, quantity	16
Dimensions	

Page 1 of 10

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 5, 2024


1 - 305



# URGRPRX7R

Cable Assembly Length Range (ft) 1 - 999

### Ordering Tree



### Mechanical Specifications

Cable Retention Strength, maximum	11.24 lb @ 0 °   4.40 lb @ 90 °
Optical Specifications	
Fiber Mode	Singlemode
Fiber Type	G.657.A2, TeraSPEED®

#### **Environmental Specifications**

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F	
Environmental Space	Dual Rated LSZH/Riser   Indoor	

#### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant
UK-ROHS	Compliant



#### Included Products

760251072 N-016-MP-8G1-F30YL/D Fiber indoor cable, TeraSPEED® Low Smoke Zero Halogen Riser for Light Duty MPO Patchcords, 16 fiber, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color, Dca

Page 2 of 10

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 5, 2024

**COMMSCOPE**<sup>®</sup>

# URGRPRX7R

860661398 860661399


#### flame rating

- Fiber Optic Connector Kit, singlemode, OS2, MPO-16/APC, ULL, pinned, green, for 3 mm cable
- Fiber Optic Connector Kit, singlemode, OS2, MPO-16/APC, ULL, unpinned, green, for 3 mm cable

Page 3 of 10



# 760251072 | N-016-MP-8G1-F30YL/D




Fiber indoor cable, TeraSPEED® Low Smoke Zero Halogen Riser for Light Duty MPO Patchcords, 16 fiber, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color, Dca flame rating

#### Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber indoor cable
Product Series	N-MP
General Specifications	
Cable Type	MPO trunk cable
Construction Type	Non-armored
Subunit Type	Gel-free
Jacket Color	Yellow
Jacket Marking	Feet
Total Fiber Count	16
Dimensions	
Diameter Over Jacket	3 mm   0.118 in

#### Representative Image



Page 4 of 10



# 760251072 | N-016-MP-8G1-F30YL/D

#### Mechanical Specifications

Minimum Bend Radius, loaded	45 mm   1.772 in
Minimum Bend Radius, unloaded	24 mm   0.945 in
Tensile Load, long term, maximum	80 N   17.985 lbf
Tensile Load, short term, maximum	267 N   60.024 lbf
Compression	4 N/mm   22.841 lb/in
Compression Test Method	FOTP-41   IEC 60794-1 E3
Flex	300 cycles
Flex Test Method	FOTP-104   IEC 60794-1 E6
Impact	0.74 N-m   6.55 in lb
Impact Test Method	FOTP-25   IEC 60794-1 E4
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33   IEC 60794-1 E1
Twist	10 cycles
Twist Test Method	FOTP-85   IEC 60794-1 E7
Vertical Rise, maximum	500 m   1,640.42 ft
Optical Specifications	

Fiber Type

G.657.A2/B2

### Environmental Specifications

Installation temperature	0 °C to +60 °C (+32 °F to +140 °F)	
Operating Temperature	0 °C to +70 °C (+32 °F to +158 °F)	
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)	
Cable Qualification Standards	ANSI/ICEA S-83-596   Telcordia GR-409	
EN50575 CPR Cable EuroClass Fire Performance	Dca	
EN50575 CPR Cable EuroClass Smoke Rating	s1a	
EN50575 CPR Cable EuroClass Droplets Rating	d0	
EN50575 CPR Cable EuroClass Acidity Rating	al	
Environmental Space	Low Smoke Zero Halogen (LSZH)   Riser	
Flame Test Listing	NEC OFNR-ST1 (ETL) and c(ETL)	
Flame Test Method	IEC 60332-3   IEC 60754-2   IEC 61034-2   UL 1666   UL 1685	

Page 5 of 10



# 760251072 | N-016-MP-8G1-F30YL/D

#### Environmental Test Specifications

Heat Age	0 °C to +85 °C (+32 °F to +185 °F)	
Heat Age Test Method	IEC 60794-1 F9	
Low High Bend	0 °C to +70 °C (+32 °F to +158 °F)	
Low High Bend Test Method FOTP-37   IEC 60794-1		
Temperature Cycle	0 °C to +70 °C (+32 °F to +158 °F)	
Temperature Cycle Test Method	FOTP-3   IEC 60794-1 F1	
Packaging and Weights		
Cable weight	8.8 kg/km   5.913 lb/kft	

#### \* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

Page 6 of 10



# 860661398



Fiber Optic Connector Kit, singlemode, OS2, MPO-16/APC, ULL, pinned, green, for 3 mm cable

#### Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America			
Portfolio	CommScope®			
Product Type	Fiber connector			

#### General Specifications

Color	Green
Color, boot	Black
Ferrule Geometry	Angled
Interface	MPO/APC Male
Interface Feature	Pinned

#### Dimensions

Compatible Cable Diameter	3 mm	0.118 in
---------------------------	------	----------

#### **Optical Specifications**

Fiber Mode	Singlemode
Fiber Type	OS2
Insertion Loss, maximum	0.3 dB
Return Loss, minimum	65 dB

#### Packaging and Weights

Packaging quantity

1

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

Page 7 of 10



### 860661398

REACH-SVHC

ROHS

UK-ROHS

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant Compliant



Page 8 of 10



# 860661399



Fiber Optic Connector Kit, singlemode, OS2, MPO-16/APC, ULL, unpinned, green, for 3 mm cable

#### Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber connector

#### General Specifications

Color	Green
Color, boot	Black
Ferrule Geometry	Angled
Interface	MPO/APC Female
Interface Feature	Unpinned

#### Dimensions

Compatible Cable Diameter	3 mm	0.118 in
---------------------------	------	----------

#### **Optical Specifications**

Fiber Mode	Singlemode
Fiber Type	OS2
Insertion Loss, maximum	0.3 dB

#### Packaging and Weights

Packaging quantity

#### Regulatory Compliance/Certifications

1

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Page 9 of 10



860661399

ROHS

UK-ROHS

Compliant Compliant



