


VZWSMART-MSK6 | BACK TO BACK CROSSOVER



BACK TO BACK CROSSOVER

Back to Back Cross Over Plate, Mounts (2) Pipes up to 4-1/2" OD to Square Tube up to 6"

Product Classification

Product Type	Clamp plate
Ordering Note	ANDREW® non-standard product

General Specifications

Mounting	Crossover plate
----------	-----------------

Dimensions

Mounting Diameter 2, maximum	152.4 mm 6 in
Mounting Diameter 2, minimum	101.6 mm 4 in
Mounting Diameter, maximum	114.3 mm 4.5 in
Mounting Diameter, minimum	88.9 mm 3.5 in

Material Specifications

Material Type	Hot dip galvanized steel
---------------	--------------------------

Environmental Specifications

EPA with 1/2 in (12 mm) radial ice	ft²
------------------------------------	-----

Packaging and Weights

Included	Plates U-bolts
Packaging quantity	1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

VZWSMART-MSK6 | BACK TO BACK CROSSOVER



* Footnotes

EPA with 1/2 in (12 mm) radial ice EPA—Effective Projected Area