

F028KKA5



FlexTwist® Flexible Twist for WR28, 37.0–40.0 GHz, with interface types PBR320 and PBR320, 1200 mm

Product Classification

Product Type	Rectangular waveguide, flexible twist
Product Brand	FlexTwist®

General Specifications

Component	Flexible Twist
Interface	PBR320
Interface 2	PBR320

Dimensions

Length	1200 mm 47.244 in
Waveguide Size	WR28 WG22 R320

Electrical Specifications

Attenuation	3.28 dB/m 1 dB/ft
Average Power	75 W
Operating Frequency Band	37.0 – 40.0 GHz
Peak Power	20 kW
VSWR	1.2

Mechanical Specifications

Minimum Bend Radius, Multiple Bends (E Plane)	38 mm 1.496 in
Minimum Bend Radius, Multiple Bends (H Plane)	76 mm 2.992 in
Maximum Twist	510 °/m 155.448 °/ft
Pressurization, maximum	0.31 N/mm ² 45 psi

F028KKA5

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

ISO 9001:2015

ROHS

Classification

Above maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant/Exempted

