

Fiber OSP cable, LightScope® ZWP Blown Micro Single Jacket, 144 fiber, All-Dielectric Stranded Loose Tube Arid-Core™ Construction, Gel-filled, Singlemode G.652.D and G.657.Al, Meters jacket marking, Black jacket color

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America

Portfolio CommScope®
Product Type Fiber OSP cable

Product Series B-LN

General Specifications

Cable Type Stranded loose tube

Construction Type Non-armored

Subunit Type Gel-filled

Filler, quantity 0

Jacket Color
Black
Jacket Marking
Meters
Jacket Marking Method
Laser

Jacket Marking Text COMMSCOPE OPTICAL CABLE OS2 SM 144F (SERIAL NUMBER) MM/YYYY XXXXXXXM

Subunit, quantity 12

Fibers per Subunit, quantity 12


Total Fiber Count 144

Dimensions

Buffer Tube/Subunit Diameter1.45 mm | 0.057 inDiameter Over Jacket8.4 mm | 0.331 in

Representative Image





Material Specifications

Jacket Material High density polyethylene (HDPE)

Mechanical Specifications

Minimum Bend Radius, loaded 126 mm | 4.961 in

Minimum Bend Radius, unloaded 84 mm | 3.307 in

Tensile Load, long term, maximum 469 N | 105.435 lbf

Tensile Load, short term, maximum 1566 N | 352.051 lbf

Compression 10 N/mm | 57.101 lb/in

Compression Test Method IEC 60794-1-21 E3

Flex 25 cycles

Flex Test Method IEC 60794-1 E6

Impact 0.3 N-m | 2.655 in lb

Impact Test Method IEC 60794-1-21 E4

Strain See long and short term tensile loads

Strain Test Method IEC 60794-1-21 E1

Twist 10 cycles

Twist Test Method IEC 60794-1-21 E7

Vertical Rise, maximum 769 m | 2,522.966 ft

Optical Specifications



Fiber Type G.652.D | G.652.D and G.657.A1

Environmental Specifications

Installation temperature $-10 \,^{\circ}\text{C}$ to $+50 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +122 $^{\circ}\text{F}$)

Operating Temperature $-30 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-22 $^{\circ}\text{F}$ to +158 $^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to +158 $^{\circ}\text{F}$)

Cable Qualification Standards IEC 60794-5-10

Environmental Space Air-blown, microduct

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Test Method FOTP-82 | IEC 60794-1 F5

Environmental Test Specifications

 Cable Freeze
 -2 °C | 28.4 °F

 Cable Freeze Test Method
 IEC 60794-1 F15

 Drip
 70 °C | 158 °F

Drip Test Method IEC 60794-1-21 E14

Heat Age -30 °C to +85 °C (-22 °F to +185 °F)

Heat Age Test Method IEC 60794-1-22 F9

Low High Bend $-30 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-22 $^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Low High Bend Test Method IEC 60794-1-21 E11

Temperature Cycle -30 °C to +70 °C (-22 °F to +158 °F)

Temperature Cycle Test Method IEC 60794-1-22 F1

Packaging and Weights

Cable weight 63 kg/km | 42.334 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Page 3 of 7





Included Products

DB-8W-LT - LightScope® ZWP Singlemode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable



LightScope® ZWP Singlemode Fiber



Product Classification

 Portfolio
 CommScope®

 Product Type
 Optical fiber

General Specifications

Cladding Diameter 125 µm **Cladding Diameter Tolerance** ±0.7 µm Cladding Non-Circularity, maximum 0.7 % **Coating Diameter (Colored)** 249 µm **Coating Diameter (Uncolored)** 242 µm **Coating Diameter Tolerance (Colored)** ±13 μm **Coating Diameter Tolerance (Uncolored)** ±5 µm Coating/Cladding Concentricity Error, maximum 12 µm **Core Diameter** 8.3 µm Core/Clad Offset, maximum $0.5 \, \mu m$

Proof Test 689.476 N/mm² | 100000 psi

Dimensions

Fiber Curl, minimum 4 m | 13.123 ft

Mechanical Specifications

 Macrobending, 20 mm Ø mandrel, 1 turn
 0.75 dB @ 1,550 nm
 1 1.50 dB @ 1,625 nm

 Macrobending, 30 mm Ø mandrel, 10 turns
 0.25 dB @ 1,550 nm
 1 1.00 dB @ 1,625 nm

 Macrobending, 60 mm Ø mandrel, 100 turns
 0.05 dB @ 1,550 nm
 0.05 dB @ 1,625 nm

Coating Strip Force, maximum8.9 N | 2.001 lbfCoating Strip Force, minimum1.3 N | 0.292 lbf

Dynamic Fatigue Parameter, minimum 20

COMMSCOPE®

DB-8W-LT

Optical Specifications

Cabled Cutoff Wavelength, maximum1260 nmPoint Defects, maximum0.1 dB

Zero Dispersion Slope, maximum 0.092 ps/[km-nm-nm]

Zero Dispersion Wavelength, maximum1324 nmZero Dispersion Wavelength, minimum1300 nm

Optical Specifications, Wavelength Specific

Attenuation, maximum 0.22 dB/km @ 1,550 nm | 0.25 dB/km @ 1,490

nm | 0.25 dB/km @ 1,625 nm | 0.36 dB/km @ 1,310

nm | 0.36 dB/km @ 1,385 nm

Attenuation, typical 0.19 dB/km @ 1,550 nm | 0.33 dB/km @ 1,310 nm

Backscatter Coefficient -79.6 dB @ 1,310 nm | -82.1 dB @ 1,550 nm

Dispersion, maximum 18 ps(nm-km) at 1550 nm | 3.5 ps(nm-km) from 1285

nm to 1330 nm at 1310 nm

Index of Refraction 1.467 @ 1,310 nm | 1.467 @ 1,385 nm | 1.468 @ 1,550

nm

1,385 nm

@ 1385 nm

Polarization Mode Dispersion Link Design Value, maximum 0.04 ps/sgrt(km)

Standards Compliance ITU-T G.652.D | ITU-T G.657.A1

Environmental Specifications

Heat Aging, maximum 0.05 dB/km @ 85 °C

 Temperature Dependence, maximum
 0.05 dB/km

 Temperature Humidity Cycling, maximum
 0.05 dB/km

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

* Footnotes

COMMSCOPE®

DB-8W-LT

Temperature Dependence, maximum

Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

Temperature Humidity Cycling, maximum Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

up to 95% relative humidity

