

F034KKS3



FlexTwist® Flexible Twist for WR34, 22.0–33.0 GHz, with interface types PBR260 and PBR260, 900 mm

Product Classification

Product Type	Rectangular waveguide, flexible twist
Product Brand	FlexTwist®

General Specifications

Component	Flexible Twist
Interface	PBR260
Interface 2	PBR260

Dimensions

Length	900 mm 35.433 in
Waveguide Size	WR34 WG21 R260

Electrical Specifications

Attenuation	2.95 dB/m 0.899 dB/ft
Average Power	75 W
Operating Frequency Band	22.0 – 33.0 GHz
Peak Power	20 kW
VSWR	1.25

Mechanical Specifications

Minimum Bend Radius, Multiple Bends (E Plane)	38 mm 1.496 in
Minimum Bend Radius, Multiple Bends (H Plane)	76 mm 2.992 in
Maximum Twist	510 °/m 155.448 °/ft
Pressurization, maximum	0.31 N/mm ² 45 psi

Regulatory Compliance/Certifications

F034KKS3

Agency

CHINA-ROHS

ISO 9001:2015

ROHS

UK-ROHS

Classification

Above maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant/Exempted

Compliant/Exempted

