# HCA-AO1V



# Fiber Optic Drop Cable Assembly, PRODIGY™ Connector Core to Stub, EZ AXS Dielectric Cable

- Cable assembly with the Prodigy™ small form hardened connector
- Compact and small footprint, space-saving design for high-density environments
- Compatible with multiple hardened connectors

#### **Product Classification**

Regional Availability Latin America | North America

**Product Type** Fiber drop cable assembly

Product Brand PRODIGY™

Product Series HCA

### General Specifications

Cable TypeDielectric - EZ Axs

Connector A, quantity

Color, boot A Black

Color, connector A Black

Interface, Connector A Prodigy®

Interface, Connector B Unterminated

Jacket Color Black

Total Fibers, quantity 1

#### Dimensions


Cable Assembly Length Range (ft) 1 - 2000

**Cable Outer Diameter** 6.0 mm (0.24 in)


# Outline Drawing



# HCA-AO1V



### Ordering Tree



## Mechanical Specifications

Minimum Bend Radius, loaded60 mm | 2.362 inMinimum Bend Radius, unloaded60 mm | 2.362 inTensile Load, long term, maximum400 N | 89.924 lbf

Page 2 of 3

# HCA-AO1V

Tensile Load, short term, maximum 1350 N | 303.492 lbf

Cable Crush Resistance, maximum10 N/mm | 57.101 lb/in

**Dust Cap Pulling Force, minimum** 445 N | 100.04 lbf

Mating Durability, maximum 0.5 dB @ 100 cycles

**Optical Specifications** 

**Fiber Mode** Singlemode

**Fiber Type** G.657.A2/B2

**Insertion Loss, maximum, connector A** 0.4 dB

**Insertion Loss, typical** 0.15 dB

**Return Loss, minimum, connector A** 65 dB

### **Environmental Specifications**

**Installation temperature** -30 °C to +60 °C (-22 °F to +140 °F)

**Operating Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

**Storage Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$ 

**Environmental Space** Outdoor

Jacket UV Resistance UV stabilized

**Qualification Standards** Telcordia GR-3120-CORE

Packaging and Weights

**Cable weight** 19 kg/km | 12.767 lb/kft