
## U3GQPQXTN

#### **Base Product**



Ultra Low Loss (ULL) Singlemode MPO8 (Non-Pinned) to MPO8 (Pinned), Fiber Trunk Cable Assembly, 192-Fiber, LZSH B2ca

### **Product Classification**

Regional Availability Europe

Portfolio CommScope®

 Product Type
 Fiber trunk cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales

Yellow

Representative | For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may vary based on cable configuration

### General Specifications

Connector A, quantity24Color, boot AGrayColor, connector AGreenConnector B, quantity24Color, boot BGrayColor, connector BGreenConstruction TypeStranded

 Interface, Connector A
 MPO-08/APC Female

 Interface, Connector B
 MPO-08/APC Male

Jacket Color Yellow

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 8

Total Fibers, quantity 192

**Dimensions** 

**Furcation Color** 

Breakout Length 22 in

# U3GQPQXTN


Cable Assembly Length Range (m)

3 - 305

Cable Assembly Length Range (ft)

10 - 999

### Ordering Tree



### Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

**Optical Specifications** 

Fiber Mode Singlemode

**Fiber Type** G.657.A2, TeraSPEED®

### **Environmental Specifications**

**Operating Temperature**  $-10 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (+14  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )

EN50575 CPR Cable EuroClass Fire Performance B2ca

Environmental Space Indoor | Low Smoke Zero Halogen (LSZH)

### Regulatory Compliance/Certifications

## Agency Classification

ANATEL Compliant

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



# U3GQPQXTN

### Included Products

760253754 – Fiber indoor cable, Low Smoke Zero Halogen Riser MPO Trunk, 192 fiber with 2.0 mm Subunits, N-192-MP-8G1-F08YL/20T/B2 Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color, B2ca flame rating

860659022 – MPO-08, ULTRA LOW LOSS, MALE, Singlemode, GREEN, 2mm 860659028 – MPO-08, ULTRA LOW LOSS, FEMALE, Singlemode, GREEN, 2mm



## 760253754 | N-192-MP-8G1-F08YL/20T/B2



Fiber indoor cable, Low Smoke Zero Halogen Riser MPO Trunk, 192 fiber with 2.0 mm Subunits, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color, B2ca flame rating

### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA

 Portfolio
 CommScope®

 Product Type
 Fiber indoor cable

**Product Series** N-MP

General Specifications

Cable TypeMPO trunk cableConstruction TypeNon-armoredSubunit TypeGel-freeJacket ColorYellowJacket MarkingFeet

Subunit, quantity 24

Fibers per Subunit, quantity 8

Total Fiber Count 192

**Dimensions** 

Buffer Tube/Subunit Diameter2 mm | 0.079 inDiameter Over Jacket14.7 mm | 0.579 in

Mechanical Specifications

Minimum Bend Radius, loaded221 mm | 8.701 inMinimum Bend Radius, unloaded147 mm | 5.787 inTensile Load, long term, maximum200 N | 44.962 lbfTensile Load, short term, maximum667 N | 149.948 lbfCompression10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Page 4 of 10

## 760253754 | N-192-MP-8G1-F08YL/20T/B2

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 99 m | 324.803 ft

Optical Specifications

**Fiber Type** G.657.A2/B2

**Environmental Specifications** 

Installation temperature0 °C to +60 °C (+32 °F to +140 °F)Operating Temperature0 °C to +70 °C (+32 °F to +158 °F)

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

EN50575 CPR Cable EuroClass Fire PerformanceB2caEN50575 CPR Cable EuroClass Smoke Ratings1aEN50575 CPR Cable EuroClass Droplets Ratingd1EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Dual Rated LSZH/Riser | Low Smoke Zero Halogen (LSZH) | Riser

Flame Test Listing NEC OFNR-ST1 (ETL) and c(ETL)

Flame Test Method CSA FT4 | IEC 60332-3 | IEC 60754-2 | IEC 61034-2 | UL

1666 | UL 1685

**Environmental Test Specifications** 

**Low High Bend** 0 °C to +70 °C (+32 °F to +158 °F)

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle**  $0 \,^{\circ}\text{C to } +70 \,^{\circ}\text{C (+32 °F to } +158 \,^{\circ}\text{F)}$ 

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

**Cable weight** 205.7 kg/km | 138.224 lb/kft

Page 5 of 10

# 760253754 | N-192-MP-8G1-F08YL/20T/B2

\* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable



### MPO-08, ULTRA LOW LOSS, MALE, Singlemode, GREEN, 2mm

### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

PortfolioCommScope®Product TypeFiber connectorProduct BrandTeraSPEED®

General Specifications

ColorGreenColor, bootBlackFerrule GeometryAngled

Interface MPO/APC Male

Interface Feature Pinned

Total Fiber Count 8

**Dimensions** 

**Compatible Cable Diameter** 2 mm | 0.079 in

Material Specifications

Ferrule Material Polymer

Optical Specifications

Fiber ModeSinglemodeFiber TypeG.657.A2

**Optical Components Standard** ANSI/TIA-568-C.3

Insertion Loss, maximum0.35 dBReturn Loss, minimum65 dB

Packaging and Weights

### **Packaging quantity**

1

## Regulatory Compliance/Certifications

Agency	Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant





### MPO-08, ULTRA LOW LOSS, FEMALE, Singlemode, GREEN, 2mm

### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

PortfolioCommScope®Product TypeFiber connectorProduct BrandTeraSPEED®

General Specifications

ColorGreenColor, bootBlackFerrule GeometryAngled

Interface MPO/APC Female

Interface Feature Unpinned

Total Fiber Count 8

**Dimensions** 

**Compatible Cable Diameter** 2 mm | 0.079 in

Material Specifications

Ferrule Material Polymer

Optical Specifications

**Fiber Mode** Singlemode Fiber Type G.657.A2

**Optical Components Standard** ANSI/TIA-568-C.3

Insertion Loss, maximum0.35 dBReturn Loss, minimum65 dB

Packaging and Weights

### **Packaging quantity**

1

## Regulatory Compliance/Certifications

Compliant

AgencyClassificationCHINA-ROHSBelow maximum concentration valueISO 9001:2015Designed, manufactured and/or distributed under this quality management systemREACH-SVHCCompliant as per SVHC revision on www.commscope.com/ProductComplianceROHSCompliant



**UK-ROHS**