# SST-B2HAA0050HN000



SST, NOVUX™ Specialty Standard Terminal, 2-port, 1:2 Splitter, Full-size Adapters, Dielectric flat loose tube cable with Full-size Connector, 50 ft / 15 m

- NOVUX™ Hardened Multi-fiber Terminals incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Hardened connectors are factory-integrated and environmentally sealed for use in optical drop cable deployments
- Plug and play adapter ports ensure rapid cable installment in the outside plant access section of the network
- Available with flat dielectric and flat toneable/locatable dielectric cable
- NOVUX™ smaller terminal size allowing for installation in constrained spaces
- NOVUX™ terminals are available in Black (RAL# 9005) or Gray (RAL# 7035)
- CommScope Product ID plate with QR code link to product documents and C-Track

### **Product Classification**

Regional Availability

Asia | EMEA | Latin America | North America

**Product Type** Access terminal, with splitter/tap

Product Brand NOVUX™
Product Series SST

Minimum Order Quantity 1

### General Specifications

Cable Type Dielectric - Flat - Loose Tube

Cable, quantity 1

**Distribution Type** 1 x 2 splitter

**Drop Port Type**Hardened full-size SC/APC

Drop Port, quantity

**Enclosure Color** Black (RAL 9005)

Mounting Handhole | Pedestal | Pole | Strand

Port Type Hardened full-size SC/APC

Port, quantity

Stub Type Hardened full-size SC/APC

**Dimensions** 



# SST-B2HAA0050HN000

**Height** 244 mm | 9.606 in


**Width** 99 mm | 3.898 in


**Length** 64 mm | 2.5 in

Cable Length, stub 50 ft (15 m)

**Cable Outer Diameter** 4.3 x 8.0 mm (0.17 x 0.31 in)

## Dimension Drawing





# Material Specifications

**Enclosure Material Type**Hardened plastic

Optical Specifications

**Fiber Type** G.657.A1/A2

**Operating Wavelength Range** 1260 – 1635 nm

Attenuation Single Ports, maximum 4.1 dB

Attenuation Cable Coefficient, maximum 0.30 dB/km @ 1550 nm | 0.40 dB/km @ 1310 nm

Attenuation Splitter, maximum 3.7 dB

COMMSC PE°

# SST-B2HAA0050HN000

Attenuation Terminal Connectors, maximum0.4 dBInsertion Loss, Stub Connector, maximum0.4 dBReturn Loss, Single Ports, minimum55 dB

### **Environmental Specifications**

**Operating Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +65 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +149 \,^{\circ}\text{F})$ 

**Relative Humidity** 5%–100%, condensing

Environmental Space Above ground | Below ground

**Qualification Standards** IEC 60529, IP68 + 2 m waterhead | IEC 61753-1, category G

UV Resistance UV stabilized

Packaging and Weights

Packaging quantity 1

Packaging Type Box | Coiled

### Regulatory Compliance/Certifications

# AgencyClassificationCHINA-ROHSBelow maximum concentration valueISO 9001:2015Designed, manufactured and/or distributed under this quality management systemREACH-SVHCCompliant as per SVHC revision on www.commscope.com/ProductComplianceROHSCompliantUK-ROHSCompliant

