CML-H60-B



Heavy Duty Chain Mount Base Kit with Stand-off, 16 ft chain

Product Classification	
Product Type	Chain mount kit
General Specifications	
Chains, quantity	4
Pipe, quantity	0
Sectors, quantity	1
Dimensions	
Height	152.4 mm 6 in
Width	203.2 mm 8 in
Length	203.2 mm 8 in
Chain Length	4,902.2 mm 193 in
Mounting Diameter, maximum	1524 mm 60 in
Mounting Diameter, minimum	203.2 mm 8 in
Pipe Outer Diameter	114.3 mm 4.5 in
Mounting Circumference, maximum	4,775.2 mm 188 in
Mounting Circumference, minimum	635 mm 25 in
Material Specifications	
Material Type	Hot dip galvanized steel
Mechanical Specifications	
Wind Rating	125 mph (BWS) at 100 ft AGL
Wind Rating Criteria	One 8 ft standard microwave antenna, with radome and stiff arm
Wind Rating Test Method	TIA/EIA-222

Packaging and Weights

Page 1 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

CML-H60-B

Included	Chains	
Packaging quantity	1	
Weight, net	49.6 kg 109.349 lb	
Regulatory Compliance/Certifications		
Agency	Classification	
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system	
* Footnotes		

Wind Rating BWS-Base Wind Speed; FBC-Florida Building Code

Page 2 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025