

CML-L60-B



Light Duty Chain Mount Base Kit, 14 in stand-off, 16 ft chain (8" to 60" OD), Pipe ordered Separately.

Product Classification

Product Type Chain mount kit

General Specifications

Chains, quantity 2

Pipe, quantity 0

Sectors, quantity 1

Dimensions

Height 152.4 mm | 6 in

Width 203.2 mm | 8 in

Length 203.2 mm | 8 in

Chain Length 4,902.2 mm | 193 in

Mounting Diameter, maximum 1524 mm | 60 in

Mounting Diameter, minimum 203.2 mm | 8 in

Pipe Outer Diameter 114.3 mm | 4.5 in

Mounting Circumference, maximum 4,775.2 mm | 188 in

Mounting Circumference, minimum 635 mm | 25 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating 120 mph (BWS) at 100 ft AGL

Wind Rating Criteria One 96 in x 10 in panel antenna per sector

Wind Rating Test Method TIA/EIA-222

CML-L60-B

Packaging and Weights

Included	Brackets Chains Hardware
Packaging quantity	1
Weight, net	18.1 kg 39.904 lb

* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code