

# NNHH-65B-R2



8-port sector antenna, 4x 698–896 and 4x 1695–2360 MHz, 65° HPBW, 2x RETs

- Array configuration provides capability for 4T4R (4x MIMO) on Low band and Mid band
- Optimized SPR performance across all operating bands
- Excellent wind loading characteristics

## General Specifications

<b>Antenna Type</b>	Sector
<b>Band</b>	Multiband
<b>Color</b>	Light Gray (RAL 7035)
<b>Grounding Type</b>	RF connector inner conductor and body grounded to reflector and mounting bracket
<b>Performance Note</b>	Outdoor usage
<b>Radome Material</b>	Fiberglass, UV resistant
<b>Radiator Material</b>	Low loss circuit board
<b>Reflector Material</b>	Aluminum
<b>RF Connector Interface</b>	4.3-10 Female
<b>RF Connector Location</b>	Bottom
<b>RF Connector Quantity, mid band</b>	4
<b>RF Connector Quantity, low band</b>	4
<b>RF Connector Quantity, total</b>	8

## Remote Electrical Tilt (RET) Information

<b>RET Hardware</b>	CommRET v2
<b>RET Interface</b>	8-pin DIN Female   8-pin DIN Male
<b>RET Interface, quantity</b>	1 female   1 male
<b>Input Voltage</b>	10–30 Vdc
<b>Internal RET</b>	Low band (1)   Mid band (1)
<b>Power Consumption, active state, maximum</b>	10 W
<b>Power Consumption, idle state, maximum</b>	2 W
<b>Protocol</b>	3GPP/AISG 2.0 (Multi-RET)

# NNHH-65B-R2

## Dimensions

<b>Width</b>	498 mm   19.606 in
<b>Depth</b>	197 mm   7.756 in
<b>Length</b>	1828 mm   71.969 in
<b>Net Weight, antenna only</b>	31 kg   68.343 lb

## Array Layout



Array ID	Frequency (MHz)	RF Connector	RET (MRET)	AISG No.	AISG RET UID
R1	698-896	1 - 2	1	AISG1	CPxxxxxxxxxxxxMM.1
R2	698-896	3 - 4			
Y1	1695-2360	5 - 6	2	AISG1	CPxxxxxxxxxxxxMM.2
Y2	1695-2360	7 - 8			

(Sizes of colored boxes are not true depictions of array sizes)

## Port Configuration



## Electrical Specifications

<b>Impedance</b>	50 ohm
<b>Operating Frequency Band</b>	1695 – 2360 MHz   698 – 896 MHz

# NNHH-65B-R2

<b>Polarization</b>	±45°
<b>Total Input Power, maximum</b>	900 W @ 50 °C

## Electrical Specifications

	<b>R1,R2</b>	<b>R1,R2</b>	<b>Y1,Y2</b>	<b>Y1,Y2</b>	<b>Y1,Y2</b>	<b>Y1,Y2</b>
<b>Frequency Band, MHz</b>	<b>698–806</b>	<b>806–896</b>	<b>1695–1880</b>	<b>1850–1990</b>	<b>1920–2180</b>	<b>2300–2360</b>
<b>RF Port</b>	1,2,3,4	1,2,3,4	5,6,7,8	5,6,7,8	5,6,7,8	5,6,7,8
<b>Gain, dBi</b>	14.6	15	17	17.3	17.5	17.9
<b>Beamwidth, Horizontal, degrees</b>	66	64	58	61	63	59
<b>Beamwidth, Vertical, degrees</b>	11.9	10.3	7.4	6.9	6.4	5.7
<b>Beam Tilt, degrees</b>	2–14	2–14	0–10	0–10	0–10	0–10
<b>USLS (First Lobe), dB</b>	17	19	14	19	16	18
<b>Front-to-Back Ratio at 180°, dB</b>	30	31	35	38	37	34
<b>Isolation, Cross Polarization, dB</b>	25	25	25	25	25	25
<b>Isolation, Inter-band, dB</b>	25	25	25	25	25	25
<b>VSWR   Return loss, dB</b>	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
<b>PIM, 3rd Order, 2 x 20 W, dBc</b>	-150	-150	-150	-150	-150	-150
<b>Input Power per Port at 50°C, maximum, watts</b>	300	300	250	250	250	200

## Mechanical Specifications

<b>Effective Projective Area (EPA), frontal</b>	0.58 m <sup>2</sup>   6.243 ft <sup>2</sup>
<b>Effective Projective Area (EPA), lateral</b>	0.18 m <sup>2</sup>   1.938 ft <sup>2</sup>
<b>Wind Loading @ Velocity, frontal</b>	622.0 N @ 150 km/h (139.8 lbf @ 150 km/h)
<b>Wind Loading @ Velocity, lateral</b>	188.0 N @ 150 km/h (42.3 lbf @ 150 km/h)
<b>Wind Loading @ Velocity, maximum</b>	746.0 N @ 150 km/h (167.7 lbf @ 150 km/h)
<b>Wind Loading @ Velocity, rear</b>	428.0 N @ 150 km/h (96.2 lbf @ 150 km/h)
<b>Wind Speed, maximum</b>	241.4 km/h (150 mph)

## Packaging and Weights

<b>Width, packed</b>	565 mm   22.244 in
<b>Depth, packed</b>	309 mm   12.165 in
<b>Length, packed</b>	2015 mm   79.331 in

# NNHH-65B-R2

---

**Weight, gross**

42.6 kg | 93.917 lb

## Regulatory Compliance/Certifications

**Agency**

**Classification**

CHINA-ROHS

Above maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted



## Included Products

BSAMNT-2F

- Mounting bracket for cylindrical pipe installations (60-115mm pipe diameter) for fix mechanical tilt applications.

## \* Footnotes

**Performance Note**

Severe environmental conditions may degrade optimum performance