


# 760254766 | C-004-CN-5K-M04BK/28D/GY/D



Indoor/Outdoor Low Smoke Zero Halogen, LazrSPEED® Central Loose Tube Fiber Optic Cable, 4-fiber, Multimode OM4, Gel-free, black. Provides Rodent Resistance.

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA
Portfolio	CommScope®
Product Type	Fiber indoor/outdoor cable
Product Series	C-CN

## General Specifications

Cable Type	Loose tube
Subunit Type	Gel-free
Jacket Color	Black
Jacket Marking	Meters
Jacket Marking Method	Inkjet
Jacket Marking Text	COMMScope GB OPTICAL CABLE 760254766 INT/EXT RODENT RESIST DLT 4X50/125 OM4 (Serial number) (metre mark)
Fibers per Subunit, quantity	4
Total Fiber Count	4

## Dimensions

Cable Length	2000 m   6,561.68 ft
Diameter Over Jacket	6.4 mm   0.252 in

## Material Specifications

Jacket Material	UV resistant
-----------------	--------------

## Mechanical Specifications

Minimum Bend Radius, loaded	139.7 mm   5.5 in
Minimum Bend Radius, unloaded	129.5 mm   5.098 in
Tensile Load, long term, maximum	650 N   146.126 lbf

760254766 | C-004-CN-5K-M04BK/28D/GY/D

Tensile Load, short term, maximum1250 N | 281.011 lbf

Optical Specifications

Fiber TypeOM4

Optical Specifications, Wavelength Specific

Attenuation, maximum1.00 dB/km @ 1,300 nm | 3.50 dB/km @ 850 nm

Standards ComplianceTIA-492AAAD (OM4)

Environmental Specifications

Operating Temperature-10 °C to +70 °C (+14 °F to +158 °F)

EN50575 CPR Cable EuroClass Fire PerformanceDca

EN50575 CPR Cable EuroClass Smoke RatingS2

EN50575 CPR Cable EuroClass Droplets Ratingd2

EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental SpaceLow Smoke Zero Halogen (LSZH)

Packaging and Weights

Cable weight47 kg/km | 31.583 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



Included Products

CS-5K-LT – LazrSPEED® 550 OM4 Bend-Insensitive Multimode Fiber

\* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable