## 760254780 | C-004-CN-5L-M04BK/28G/GY/E



Indoor/Outdoor Low Smoke Zero Halogen, LazrSPEED® Central Loose Tube Fiber Optic Cable, 4-fiber, Multimode OM3, Gel-filled, black. Provides Rodent Resistance.

### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA

Portfolio CommScope®

Product Type Fiber indoor/outdoor cable

**Product Series** C-CN

General Specifications

Cable TypeLoose tubeSubunit TypeGel-filledJacket ColorBlackJacket MarkingMetersJacket Marking MethodInkjet

Jacket Marking Text COMMSCOPE GB OPTICAL CABLE 760254780 INT/EXT RODENT RESIST

GLT 4X50/125 OM3 (Serial NUMBER) (METRE MARK)

Fibers per Subunit, quantity 4

Total Fiber Count 4

**Dimensions** 

 Cable Length
 2000 m | 6,561.68 ft

 Diameter Over Jacket
 6.4 mm | 0.252 in

Mechanical Specifications

Minimum Bend Radius, loaded129.5 mm | 5.098 inMinimum Bend Radius, unloaded80 mm | 3.15 inTensile Load, long term, maximum650 N | 146.126 lbfTensile Load, short term, maximum1250 N | 281.011 lbf

Optical Specifications



# 760254780 | C-004-CN-5L-M04BK/28G/GY/E

Fiber Type OM3

Optical Specifications, Wavelength Specific

**Attenuation, maximum** 0.70 dB/km @ 1,300 nm | 3.50 dB/km @ 850 nm

Standards Compliance TIA-492AAAC (OM3)

**Environmental Specifications** 

**Operating Temperature**  $-20 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C} \left(-4 \,^{\circ}\text{F to} + 158 \,^{\circ}\text{F}\right)$ 

**EN50575 CPR Cable EuroClass Fire Performance** Eca

Environmental Space Low Smoke Zero Halogen (LSZH)

Packaging and Weights

**Cable weight** 48 kg/km | 32.255 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



#### Included Products

CS-5L-TB – LazrSPEED® 300 OM3 Bend-Insensitive Multimode

Fiber

### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

