760254782 | C-006-CN-5L-M06BK/28G/GY/E



Indoor/Outdoor Low Smoke Zero Halogen, LazrSPEED® Central Loose Tube Fiber Optic Cable, Multimode OM3, 6-fiber, black. Provides Rodent Resistance.

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA

Portfolio CommScope®

Product Type Fiber indoor/outdoor cable

Product Series C-CN

General Specifications

Cable TypeLoose tubeSubunit TypeGel-filled

Filler, quantity 1

Jacket ColorBlackJacket MarkingMetersJacket Marking MethodInkjet

Jacket Marking Text COMMSCOPE GB OPTICAL CABLE 760254782 INT/EXT RODENT RESIST

GLT 6X50/125 OM3 (Serial NUMBER) (METRE MARK)

Fibers per Subunit, quantity 6

Total Fiber Count 6

Dimensions

 Cable Length
 2000 m | 6,561.68 ft

 Diameter Over Jacket
 6.4 mm | 0.252 in

Mechanical Specifications

Minimum Bend Radius, loaded129.5 mm | 5.098 inMinimum Bend Radius, unloaded80 mm | 3.15 inTensile Load, long term, maximum650 N | 146.126 lbfTensile Load, short term, maximum1250 N | 281.011 lbf



760254782 | C-006-CN-5L-M06BK/28G/GY/E

Optical Specifications

Fiber Type OM3

Optical Specifications, Wavelength Specific

Attenuation, maximum 1.00 dB/km @ 1,300 nm | 3.50 dB/km @ 850 nm

Standards Compliance IEC 60794-1 | TIA-492AAAC (OM3)

Environmental Specifications

Installation temperature $-5 \,^{\circ}\text{C}$ to $+50 \,^{\circ}\text{C}$ (+23 $^{\circ}\text{F}$ to +122 $^{\circ}\text{F}$)

Operating Temperature $-20 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-4 $^{\circ}\text{F}$ to +158 $^{\circ}\text{F}$)

Storage Temperature $-20 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-4 $^{\circ}\text{F}$ to +158 $^{\circ}\text{F}$)

EN50575 CPR Cable EuroClass Fire Performance Eca

Environmental Space Low Smoke Zero Halogen (LSZH)

Packaging and Weights

Cable weight 48 kg/km | 32.255 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

CS-5L-TB – LazrSPEED® 300 OM3 Bend-Insensitive Multimode

Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

