760254806 | C-004-DS-8G-MSUBK/GY/C



Indoor/Outdoor Low Smoke Zero Halogen, LazrSPEED® Tight Buffered Office DistributionFiber Fiber Optic Cable, 4 fiber, Singlenode G.657.A2, black. Provides Rodent Resistance.

- designed to offer flexibility, strength and compact construction for internal and interbuilding use
- non-metallic construction reinforced by E-glass yarns, which provide rodent resistance and higher tensile strength
- oversheathed with a ULSZH jacket meeting IEC fire performance requirements

Product Classification

| Regional Availability | Asia EMEA |
|------------------------------|--|
| Portfolio | CommScope® |
| Product Type | Fiber indoor/outdoor cable |
| Product Series | C-DS |
| General Specifications | |
| Cable Type | Tight buffer |
| Jacket Color | Black |
| Jacket Marking | Meters |
| Jacket Marking Method | Inkjet |
| Jacket Marking Text | COMMSCOPE GB OPTICAL CABLE 760254806 4x9/125 G.657A2 EN50575 CLASS C ULSZH (Serial NUMBER) (METRE MARK) |
| Strength Members | E-glass yarns |
| Fibers per Subunit, quantity | 4 |
| Total Fiber Count | 4 |
| Dimensions | |
| Diameter Over Jacket | 5.5 mm 0.217 in |
| | |


Representative Image

Page 1 of 5

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 1, 2025



760254806 | C-004-DS-8G-MSUBK/GY/C



Mechanical Specifications

| Minimum Bend Radius, loaded | 130 mm 5.118 in |
|--|-------------------------------------|
| Minimum Bend Radius, unloaded | 80 mm 3.15 in |
| Tensile Load, short term, maximum | 1000 N 224.809 lbf |
| Cable Crush Resistance, maximum | 20 N/mm 114.203 lb/in |
| Optical Specifications | |
| Fiber Type | G.657.A2 |
| Optical Specifications, Wavelength Specific | |
| Standards Compliance | IEC 60794-1 ITU-T G.657.A2 |
| | |
| Environmental Specifications | |
| Installation temperature | -5 °C to +50 °C (+23 °F to +122 °F) |
| Operating Temperature | -20 °C to +60 °C (-4 °F to +140 °F) |
| Storage Temperature | -20 °C to +60 °C (-4 °F to +140 °F) |
| EN50575 CPR Cable EuroClass Fire Performance | Сса |
| EN50575 CPR Cable EuroClass Smoke Rating | s2 |
| EN50575 CPR Cable EuroClass Droplets Rating | d1 |
| EN50575 CPR Cable EuroClass Acidity Rating | a1 |
| Environmental Space | Low Smoke Zero Halogen (LSZH) |

Page 2 of 5

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 1, 2025



760254806 | C-004-DS-8G-MSUBK/GY/C

Packaging and Weights

Cable weight

33 kg/km | 22.175 lb/kft

Included Products

CS-8G-TB

Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T G.657.A2, B2)

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

Page 3 of 5

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 1, 2025



CS-8G-TB

Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T G. 657.A2, B2)

Product Classification

| Portfolio | CommScope® |
|---|---|
| Product Type | Optical fiber |
| General Specifications | |
| Cladding Diameter | 125 µm |
| Cladding Diameter Tolerance | ±0.7 µm |
| Cladding Non-Circularity, maximum | 0.7 % |
| Coating Diameter (Colored) | 249 μm |
| Coating Diameter (Uncolored) | 242 µm |
| Coating Diameter Tolerance (Colored) | ±13 μm |
| Coating Diameter Tolerance (Uncolored) | ±5 μm |
| Coating/Cladding Concentricity Error, maximum | 12 µm |
| Core/Clad Offset, maximum | 0.5 µm |
| Proof Tensile Stress | 100,000 psi (0.69 GPa) |
| Dimensions | |
| Fiber Curl, minimum | 4 m 13.123 ft |
| Mechanical Specifications | |
| Macrobending, 15 mm Ø mandrel, 1 turn | 0.50 dB @ 1,550 nm 1.00 dB @ 1,625 nm |
| Macrobending, 20 mm Ø mandrel, 1 turn | 0.10 dB @ 1,550 nm 0.20 dB @ 1,625 nm |
| Macrobending, 30 mm Ø mandrel, 10 turns | 0.03 dB @ 1,550 nm 0.10 dB @ 1,625 nm |
| Coating Strip Force, maximum | 8.9 N 2.001 lbf |
| Coating Strip Force, minimum | 1.3 N 0.292 lbf |
| Dynamic Fatigue Parameter, minimum | 20 |
| Optical Specifications | |
| Cabled Cutoff Wavelength, maximum | 1260 nm |
| Point Defects, maximum | 0.1 dB |

Page 4 of 5

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 30, 2025



CS-8G-TB

| Zero Dispersion Slope, maximum | 0.092 ps/[km-nm-nm] | |
|---|---|--|
| Zero Dispersion Wavelength, maximum | 1324 nm | |
| Zero Dispersion Wavelength, minimum | 1302 nm | |
| Optical Specifications, Wavelength Specific | | |
| Attenuation, maximum | 0.50 dB/km @ 1,310 nm 0.50 dB/km @ 1,385 nm 0.50 dB/km @ 1,550 nm | |
| Dispersion, maximum | 18 ps(nm-km) at 1550 nm 3.5 ps(nm-km) from 1285 nm to 1330 nm at 1310 nm | |
| Index of Refraction | 1.467 @ 1,310 nm 1.467 @ 1,385 nm 1.468 @ 1,550 nm | |
| Mode Field Diameter | 8.6 μm @ 1,310 nm 9.8 μm @ 1,550 nm | |
| Mode Field Diameter Tolerance | ±0.4 μm @ 1310 nm ±0.5 μm @ 1550 nm | |
| Polarization Mode Dispersion Link Design Value, maximum | 0.06 ps/sqrt(km) | |
| Standards Compliance | ITU-T G.657.A2 ITU-T G.657.B2 | |

Environmental Specifications

| Heat Aging, maximum | 0.05 dB/km @ 85 °C |
|---------------------------------------|--------------------|
| Temperature Dependence, maximum | 0.05 dB/km |
| Temperature Humidity Cycling, maximum | 0.05 dB/km |
| Water Immersion, maximum | 0.05 dB/km @ 23 °C |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

* Footnotes

| Temperature Dependence, maximum | Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F) |
|---------------------------------------|---|
| Temperature Humidity Cycling, maximum | Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F) up to 95% relative humidity |

Page 5 of 5

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 30, 2025

