
## **ALGLGUCCM**

#### **Base Product**



Ultra Low Loss ULL TeraSPEED® LC/UPC to Unconnectorized Ruggedized fanout Cable, 144-Fiber, Plenum, 12 fiber PmP 2.0 mm Dca

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle

East/Africa | North America

Portfolio CommScope®

**Product Type** Ruggedized fanout

Product Brand SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales

Yellow

Representative | For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may vary based on cable configuration

### General Specifications

Color, boot A Blue

Color, connector A Green

Color, boot B Blue

Color, connector B Blue

Construction Type Stranded

Interface, Connector A LC/APC

Interface Feature, connector A ULL

Interface, Connector B Unterminated

Interface Feature, connector B ULL

Jacket Color Yellow

Fibers per Subunit, quantity 12

Total Fibers, quantity 144

#### **Dimensions**

**Furcation Color** 

Cable Assembly Length Range (m) 3 - 999
Cable Assembly Length Range (ft) 8 - 999

Page 1 of 5



# **ALGLGUCCM**

### **Optical Specifications**

Fiber Mode Singlemode

**Fiber Type** G.657.A2, TeraSPEED®

**Environmental Specifications** 

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

EN50575 CPR Cable EuroClass Fire Performance Doa

Environmental Space Indoor | Plenum

### Regulatory Compliance/Certifications

Agency Classification

ANATEL Compliant



#### Included Products

760242061 P-144-MP-8G-F12YL/20T Fiber Indoor Cable, Plenum MPO Trunk, 144 fiber multi-unit with 12 fiber subunits, Singlemode
 G.657.A2/B2, Gel-free, Feet jacket marking, Yellow jacket color

# 760242061 | P-144-MP-8G-F12YL/20T



Fiber Indoor Cable, Plenum MPO Trunk, 144 fiber multi-unit with 12 fiber subunits, Singlemode G.657.A2/B2, Gel-free, Feet jacket marking, Yellow jacket color

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber indoor cable

**Product Series** P-MP

General Specifications

Cable TypeMPO trunk cable

Construction Type Non-armored

**Subunit Type** Gel-free

Jacket Color Yellow

Jacket Marking Feet

Subunit, quantity 12

Fibers per Subunit, quantity 12

Total Fiber Count 144

**Dimensions** 


**Buffer Tube/Subunit Diameter** 2 mm | 0.079 in

**Diameter Over Jacket** 11.8 mm | 0.465 in

Representative Image



# 760242061 | P-144-MP-8G-F12YL/20T



### Mechanical Specifications

Minimum Bend Radius, loaded 172 mm | 6.772 in

Minimum Bend Radius, unloaded 115 mm | 4.528 in

Tensile Load, long term, maximum 200 N | 44.962 lbf

**Tensile Load, short term, maximum** 667 N | 149.948 lbf

**Compression** 10 N/mm | 57.101 lb/in

**Compression Test Method** FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 0.74 N-m | 6.55 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 500 m | 1,640.42 ft

**Optical Specifications** 

**Fiber Type** G.657.A2/B2 | G.657.A2/B2

**Environmental Specifications** 

**Installation temperature**  $0 \, ^{\circ}\text{C} \text{ to } +70 \, ^{\circ}\text{C} \text{ (+32 } ^{\circ}\text{F to } +158 \, ^{\circ}\text{F)}$ 

COMMSC PE°

# 760242061 | P-144-MP-8G-F12YL/20T

**Operating Temperature**  $0 \, ^{\circ}\text{C to } +70 \, ^{\circ}\text{C (} +32 \, ^{\circ}\text{F to } +158 \, ^{\circ}\text{F)}$ 

**Storage Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

Environmental Space Plenum

Flame Test Listing

NEC OFNP (ETL) and c(ETL)

Flame Test Method

NFPA 130 | NFPA 262

**Environmental Test Specifications** 

**Heat Age** 0 °C to +85 °C (+32 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

**Low High Bend**  $0 \,^{\circ}\text{C to } +70 \,^{\circ}\text{C (+32 °F to } +158 \,^{\circ}\text{F)}$ 

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle** 0 °C to +70 °C (+32 °F to +158 °F)

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

**Cable weight** 143 kg/km | 96.092 lb/kft

### Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

#### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

