


2160852-2 | OCP-LF-02MASEN-XX



Fiber Optic Pigtail, Simplex, Singlemode, LC/UPC to Stub, 0.9 mm diameter, 2 m

Product Classification

Regional Availability	EMEA
Product Type	Fiber pigtail, jacketed
Product Series	OCP

General Specifications

Connector A, quantity	1
Color, boot A	Blue
Color, connector A	Blue
Interface, Connector A	LC/UPC
Jacket Color	Yellow
Total Fibers, quantity	1

Dimensions

Cord Length	2 m 6.562 ft
--------------------	----------------

Ordering Tree

2160852-2 | OCP-LF-02MASEN-XX



Connector/adaptor type		
Standard C grade	Superior B grade	Type
S1	SF	SC/UPC
S2	SG	SC/APC 8°
S3	SH	SC/APC 9°
L1	LF	LC/UPC
L2	LG	LC/APC
-	EC	LSH/APC 8°

Cable type			Fiber type
ASEN	900 μm	Semi-tight jacket	A1
HSEN	900 μm	Semi-tight jacket	A2

Cable length	
02	2 meters

- Standard Configuration by default 900μm buffer
 buffer color : yellow
 250 μm color : natural or milky white

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A1, TeraSPEED®
Performance Grade	Superior B grade

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
----------------------------	-------------------------------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant/Exempted



* Footnotes

2160852-2 | OCP-LF-02MASEN-XX

Performance Grade Guarantee to meet IEC 61755-1 Random Mating requirement