# \_4NF-F



#### N Female for 1/2 in LDF4-50A cable

#### **Product Classification**

**Product Type** Wireless and radiating connector

**Product Brand HELIAX® Product Series** LDF4-50A

**Ordering Note** ANDREW® standard product (Global)

Silver

Trimetal

Warranty Five years

General Specifications

**Body Style** Straight LDF4-50A **Cable Family Inner Contact Attachment Method** Captivated

**Inner Contact Plating** Interface N Female

**Mounting Angle** Straight **Outer Contact Attachment Method** Clamp

**Dimensions** 


**Outer Contact Plating** 

Length 61.7 mm | 2.429 in Diameter 23 mm | 0.906 in

**Nominal Size** 1/2 in

Outline Drawing





# **Electrical Specifications**

**3rd Order IMD** -159 dBc

**3rd Order IMD at Frequency** -116 dBm @ 900 MHz

**3rd Order IMD Test Method** Two +43 dBm carriers

**Insertion Loss Coefficient, typical** 0.05

Average Power at Frequency 0.6 kW @ 900 MHz

**Connector Impedance** 50 ohm

dc Test Voltage 2000 V

**Impedance** 50 ohm

**Inner Contact Resistance, maximum** 1 m0hm

**Insulation Resistance, minimum** 5000 MOhm

**Operating Frequency Band** 0 – 8800 MHz

Outer Contact Resistance, maximum 0.25 mOhm

**RF Operating Voltage, maximum (vrms)** 707 V



# L4NF-F

## VSWR/Return

#### Loss

Frequency Band	VSWR	Return Loss (dB)	Gated VSWR	Gated Return Loss (dB)	VSWR, typical	Return Loss, typical (dB)
0-1000 MHz	1.08	28.3	1.025	38		
1000-2200 MHz	1.1	26.44	1.032	36		
2200-3000 MHz	1.1	26.44	1.036	35		
3000-4000 MHz	1.2	20.83	1.036	35		
4000-6000 MHz	1.3	17.69	1.065	30		
6000-8800 MHz			1.119	25	1.431	15.02

## Mechanical Specifications

Attachment Durability 25 cycles

Connector Retention Tensile Force600 N | 134.885 lbfConnector Retention Torque4.5 N-m | 39.828 in lb

Interface Durability 500 cycles

Interface Durability MethodIEC 61169-16:9.5Mechanical Shock Test MethodIEC 60068-2-27

# **Environmental Specifications**

Operating Temperature-55 °C to +85 °C (-67 °F to +185 °F)Storage Temperature-55 °C to +85 °C (-67 °F to +185 °F)

Corrosion Test Method IEC 60068-2-11

Immersion Depth1 mImmersion Test MatingMated

**Immersion Test Method** IEC 60529:2001, IP68

Thermal Shock Test Method IEC 60068-2-14
Vibration Test Method IEC 60068-2-6

Packaging and Weights

 Height, packed
 248.92 mm | 9.8 in

 Width, packed
 266.7 mm | 10.5 in

 Length, packed
 266.7 mm | 10.5 in

Packaging quantity 50

ANDREW® an Amphenol company

# L4NF-F

# Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



### \* Footnotes

**Warranty** For more information, please consult our Product Warranty guidelines

**Insertion Loss Coefficient, typical** 0.05√ freq (GHz) (not applicable for elliptical waveguide)

**Immersion Depth** Immersion at specified depth for 24 hours