Z-TB-5M

Base Product



LazrSPEED® 900µm Tight Buffered Fiber


Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber indoor cable

Representative Image



Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Included Products

CS-5M-TB – LazrSPEED® 150 OM2+ Bend-Insensitive Multimode

Fiber

COMMSCOPE®

LazrSPFFD® 150 OM2+ Bend-Insensitive Multimode Fiber

LazrSPFFD® 150

Product Classification

Portfolio CommScope®
Product Type Optical fiber

General Specifications

Cladding Diameter 125 µm **Cladding Diameter Tolerance** ±0.8 µm Cladding Non-Circularity, maximum 1 % **Coating Diameter (Colored)** $254 \, \mu m$ **Coating Diameter (Uncolored)** 245 µm **Coating Diameter Tolerance (Colored)** ±7 µm **Coating Diameter Tolerance (Uncolored)** ±10 μm Coating/Cladding Concentricity Error, maximum 12 µm **Core Diameter** 50 µm **Core Diameter Tolerance** ±2.5 µm Core/Clad Offset, maximum $1.5 \, \mu m$

Proof Test 689.476 N/mm² | 100000 psi

Tight Buffer Diameter 900 μm Tight Buffer Diameter Tolerance $\pm 40 \ \mu m$

Mechanical Specifications

 Macrobending, 15 mm Ø mandrel, 2 turns
 0.20 dB @ 850 nm
 0.50 dB @ 1,300 nm

 Macrobending, 30 mm Ø mandrel, 2 turns
 0.10 dB @ 850 nm
 0.30 dB @ 1,300 nm

Coating Strip Force, maximum $8.9 \, \text{N}$ $2.001 \, \text{lbf}$ Coating Strip Force, minimum $1.3 \, \text{N}$ $0.292 \, \text{lbf}$

COMMSCOPE®

CS-5M-TB

Dynamic Fatigue Parameter, minimum 18

Optical Specifications

Numerical Aperture 0.2

Numerical Aperture Tolerance±0.015Point Defects, maximum0.15 dB

Zero Dispersion Slope, maximum 0.105 ps/[km-nm-nm]

Zero Dispersion Wavelength, maximum 1316 nm **Zero Dispersion Wavelength, minimum** 1297 nm

Optical Specifications, Wavelength Specific

1 Gbps Ethernet Distance 600 m @ 1,300 nm | 800 m @ 850 nm

10 Gbps Ethernet Distance 150 m @ 850 nm

Attenuation, maximum 1.00 dB/km @ 1,300 nm | 3.00 dB/km @ 850 nm

Backscatter Coefficient -68.0 dB @ 850 nm | -75.7 dB @ 1,300 nm

 Bandwidth, Laser, minimum
 500 MHz-km @ 1,300 nm | 950 MHz-km @ 850 nm

 Bandwidth, OFL, minimum
 500 MHz-km @ 1,300 nm | 700 MHz-km @ 850 nm

 Differential Mode Delay
 0.70 ps/m @ 850 nm | 0.88 ps/m @ 1,300 nm

Index of Refraction 1.479 @ 1,300 nm | 1.483 @ 850 nm

Standards Compliance TIA-492AAAB (OM2+)

Environmental Specifications

Heat Aging, maximum $0.20 \text{ dB/km} \ @ 85 \ ^{\circ}\text{C}$

Temperature Dependence, maximum0.1 dB/kmTemperature Humidity Cycling, maximum0.2 dB/km

Water Immersion, maximum 0.20 dB/km @ 23 °C

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

* Footnotes

Temperature Dependence, maximum Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

Temperature Humidity Cycling, maximum Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

Page 3 of 4

CS-5M-TB

up to 95% relative humidity

