URGMPLUUD

Base Product



Ultra Low Loss (ULL) Singlemode MPO12 (Non-pinned) to LC Uniboot, Fiber Array Cable Assembly, 12-Fiber, Dual Rated (OFNR/LSZH)

Product Classification

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle

East/Africa | North America

Portfolio CommScope®

 Product Type
 Fiber array cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales

Representative | For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may vary based on cable configuration

General Specifications

Connector A, quantity 1

Color, boot A Black
Color, connector A Green

Connector B, quantity 6

Color, boot B Blue
Color, connector B Blue

Construction Type Stranded
Furcation Color Yellow

Interface, Connector A MPO-12/APC Female

Interface, Connector B LC/UPC

Jacket Color Yellow

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 12

Total Fibers, quantity 12

Dimensions




URGMPLUUD

Cable Assembly Length Range (m) 1 - 305

Cable Assembly Length Range (ft) 1 - 999

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 $^{\circ}$ | 4.40 lb @ 90 $^{\circ}$

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A2, TeraSPEED®

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

EN50575 CPR Cable EuroClass Fire Performance Dca

Environmental Space Dual Rated LSZH/Riser | Indoor

Regulatory Compliance/Certifications

Agency	Classification
ANATEL	Compliant
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance

COMMSCOPE®

URGMPLUUD

ROHS

Compliant

UK-ROHS

Compliant





Included Products

760245203 NL012-MD-8C1-E20VL/E Low Smoke Zero Halogen Riser Light Duty Interconnect Cable, 12 fiber


N-012-MP-8G1-F20YL/E

MPO12, ULTRA LOW LOSS, FEMALE, Singlemode, GREEN, 3mm

860638318 860658160

- LC/UPC Uniboot Connector, Singlemode, Blue

760245203 | N-012-MP-8G1-F20YL/E



Low Smoke Zero Halogen Riser Light Duty Interconnect Cable, 12 fiber

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

Portfolio CommScope®

Product Type Fiber indoor cable

Product Series N-MP

General Specifications

Cable TypeMPO trunk cable

Construction Type Non-armored


Subunit TypeGel-freeJacket ColorYellowJacket MarkingFeet

Total Fiber Count 12

Dimensions

Diameter Over Armor 2 mm | 0.079 in

Representative Image



Page 4 of 10



760245203 | N-012-MP-8G1-F20YL/E

Mechanical Specifications

Minimum Bend Radius, loaded38 mm | 1.496 inMinimum Bend Radius, unloaded16 mm | 0.63 inTensile Load, long term, maximum33 N | 7.419 lbfTensile Load, short term, maximum111 N | 24.954 lbf

Compression 4 N/mm | 22.841 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 0.74 N-m | 6.55 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 500 m | 1,640.42 ft

Optical Specifications

Fiber Type G.657.A2/B2 | G.657.A2/B2

Environmental Specifications

Installation temperature0 °C to +60 °C (+32 °F to +140 °F)Operating Temperature0 °C to +70 °C (+32 °F to +158 °F)Storage Temperature-40 °C to +70 °C (-40 °F to +158 °F)

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

EN50575 CPR Cable EuroClass Fire Performance Eca

Environmental Space Low Smoke Zero Halogen (LSZH) | Riser

Flame Test Listing NEC OFNR-ST1 (ETL) and c(ETL)

Flame Test Method | IEC 60332-3 | IEC 60754-2 | IEC 61034-2 | UL 1666 | UL 1685

Environmental Test Specifications

Heat Age 0 °C to +85 °C (+32 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

Page 5 of 10



760245203 | N-012-MP-8G1-F20YL/E

Low High Bend 0 °C to +70 °C (+32 °F to +158 °F)

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle $0 \,^{\circ}\text{C to } +70 \,^{\circ}\text{C (+32 °F to } +158 \,^{\circ}\text{F)}$

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 3.7 kg/km | 2.486 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CENELEC EN 50575 compliant, Declaration of Performance (DoP) available

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant UK-ROHS Compliant



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable





MPO12, ULTRA LOW LOSS, FEMALE, Singlemode, GREEN, 3mm

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

 Portfolio
 CommScope®

 Product Type
 Fiber connector

 Product Brand
 TeraSPEED®

General Specifications

ColorGreenColor, bootBlackFerrule GeometryAngled

Interface MPO/APC Female

Interface Feature Unpinned

Total Fiber Count 12

Dimensions

Length60.1 mm | 2.366 inCompatible Cable Diameter3 mm | 0.118 in

Material Specifications

Ferrule Material Polymer

Mechanical Specifications

Cable Retention Strength, maximum $11.24 \text{ lb} @ 0 ^{\circ}$

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.652.D and G.657.A1, TeraSPEED® | OS2

Insertion Loss Change, mating 0.3 dB

Optical Components Standard ANSI/TIA-568-C.3

Page 7 of 10

Insertion Loss Change, temperature0.3 dBInsertion Loss, maximum0.35 dBReturn Loss, minimum65 dB

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



* Footnotes

Insertion Loss Change, matingTIA-568: Maximum insertion loss change after 500 matings

 $\textbf{Insertion Loss Change, temperature} \quad \text{Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)}$





LC/UPC Uniboot Connector, Singlemode, Blue

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber connector

General Specifications

Color, bootBlueColor, housingBlueInterfaceLC/UPC

Dimensions

Length 64 mm | 2.52 in

Compatible Cable Diameter 1.6 mm | 0.063 in | 2 mm | 0.079 in

Material Specifications

Ferrule Material Zirconia

Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 °

Optical Specifications

Fiber Mode Singlemode

Insertion Loss Change, mating 0.2 dB

Optical Components Standard ANSI/TIA-568. 3-D | IEC 61753-1

Insertion Loss Change, temperature0.2 dBInsertion Loss, ULL, maximum0.25 dBReturn Loss, minimum55 dB

Regulatory Compliance/Certifications

COMMSC PE°

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



* Footnotes

Insertion Loss Change, matingTIA-568: Maximum insertion loss change after 500 matings

Insertion Loss Change, temperature Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)

