VZWSMART-SFK3-SL | V-BRACING KIT FOR SMALL LEGS



V-BRACING KIT FOR SMALL LEGS

V-Bracing Kit for Tower with saddle clamps for 1.5"- 3-1/2" OD or 3" 60 degree angle or 2-1/2" 90 degree angle Tower legs, Dual Pivoting Angle Arms, 96" long, attaches up to 4-1/2" OD horizontals

Product Classification

Product Type	Reinforcement kit	
Ordering Note	ANDREW® non-standard product	
General Specifications		
Mounting	Angle Members 38.1–76.2 mm (1-1/2 in to 3 in) Round member Round member, 38.1– 88.9 mm (1-1/2 in to 3-1/2 in) OD	
Pipe, quantity	0	
Tower Taper	Non-tapered Tapered	
Dimensions		
Mounting Diameter 2, maximum	114.3 mm 4.5 in	
Mounting Diameter, maximum	88.9 mm 3.5 in	
Mounting Diameter, minimum	38.1 mm 1.5 in	
Material Specifications		
Material Type	Hot dip galvanized steel	
Packaging and Weights		

Included	Clamps Legs Saddle mount
Packaging quantity	1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

Page 1 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

VZWSMART-SFK3-SL | V-BRACING KIT FOR SMALL LEGS



Page 2 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025