

F028MMS5



FlexTwist® Flexible Twist for WR28, 26.5–40.1 GHz, with interface types UBR320 and UBR320, 1200 mm

Product Classification

Product Type	Rectangular waveguide, flexible twist
Product Brand	FlexTwist®

General Specifications

Component	Flexible Twist
Interface	UBR320
Interface 2	UBR320

Dimensions

Length	1200 mm 47.244 in
Waveguide Size	WR28 WG22 R320

Electrical Specifications

Attenuation	3.28 dB/m 1 dB/ft
Average Power	75 W
Operating Frequency Band	26.5 – 40.1 GHz
Peak Power	20 kW
VSWR	1.3

Mechanical Specifications

Minimum Bend Radius, Multiple Bends (E Plane)	38 mm 1.496 in
Minimum Bend Radius, Multiple Bends (H Plane)	76 mm 2.992 in
Maximum Twist	510 °/m 155.448 °/ft
Pressurization, maximum	0.31 N/mm² 45 psi

F028MMS5

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

