


# SFG22HDX12-4-H10



G22HDX High Capacity Sector Frame with 2 7/8in OD x 12.5ft face.  
Includes four 2 7/8in OD x 120in antenna pipes.

## Product Classification

Product Type	High capacity Tower sector frame
Product Series	G2

## General Specifications

Mounting	Angle 60°, 203.2 mm (8 in)   Straight or tapered legs up to 203.2 mm (8 in) OD
Patent Number	Patent pending
Pipe, quantity	4
Sectors, quantity	1
Tower Taper	Non-tapered   Tapered

## Dimensions

Height	3,048 mm   120 in
Face Width	3.81 m   12.5 ft
Width	3,810 mm   150 in
Pipe Length	3,048 mm   120 in
Face Support Pipe Diameter	73.025 mm   2.875 in
Mounting Diameter, maximum	218.44 mm   8.6 in
Mounting Diameter, minimum	38.1 mm   1.5 in
Pipe Outer Diameter	73.025 mm   2.875 in
Stand-off Distance	1,066.8 mm   42 in

## Material Specifications

Material Type	Hot dip galvanized steel
---------------	--------------------------

## Mechanical Specifications

Wind Rating	For Specifications, please contact your local ANDREW representative
Wind Rating Test Method	TIA/EIA-222-G

# SFG22HDX12-4-H10

---

## Packaging and Weights

Included	Frame   Pipe mounts   Plain end pipes (4)   Stiff arms (2)   Tower attachment
Packaging quantity	1
Weight, net	311.164 kg   686 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



## \* Footnotes

Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code
-------------	--