

760254041 | EPX-1U-CHD-ENC



EPX 1U sliding panel, accepts (8) CHD style modules, adapter packs, or splice cassettes, providing up to 48 duplex LC ports

Product Classification

Regional Availability	Asia Australia/New Zealand China
Portfolio	CommScope®
Product Type	Fiber patch panel Fiber patch/splice panel
Product Series	EPX

General Specifications

Application	Accepts eight CHD modular cassettes Accepts four G2 modular cassettes
Color	Black
Intelligence Type	Not iPatch® ready
Interface, front	Unloaded
Module/Adapter Pack Slots, quantity	4
Rack Type	EIA 19 in
Rack Units	1
Shelf Movement	Sliding
Total Fibers, quantity	96

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	412.75 mm 16.25 in

Environmental Specifications

Safety Standard	CSA 22.2 UL 1863
------------------------	--------------------

Packaging and Weights

Packaging quantity	1
---------------------------	---

760254041 | EPX-1U-CHD-ENC

Weight, net

3.529 kg | 7.78 lb