

760254041 | EPX-1U-CHD-ENC



EPX 1U sliding panel, accepts (8) CHD style modules, adapter packs, or splice cassettes, providing up to 48 duplex LC ports

Product Classification

Regional Availability	Asia Australia/New Zealand China
Portfolio	CommScope®
Product Type	Fiber patch panel Fiber patch/splice panel
Product Series	EPX

General Specifications

Application	Accepts eight CHD modular cassettes Accepts four G2 modular cassettes
Color	Black
Intelligence Type	Not iPatch® ready
Interface, front	Unloaded
Module/Adapter Pack Slots, quantity	4
Rack Type	EIA 19 in
Rack Units	1
Shelf Movement	Sliding
Total Fibers, quantity	96
Total Ports, quantity	0

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	412.75 mm 16.25 in

Environmental Specifications

Safety Standard	CSA 22.2 UL 1863
-----------------	--------------------

Packaging and Weights

Packaging quantity

1

Weight, net

3.529 kg | 7.78 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

