


# MC-CP14S-12-96



3-Sector Monopole Co-location Platform Kit, 10 in to 30 in OD, 14 ft 6 in face, includes twelve 96 in pipes

**OBSOLETE**

This product was discontinued on: March 9, 2022

**Replaced By:**

MC-CP14M-12-96      3-Sector Monopole Co-location Platform Kit, 12 in to 50 in OD, 14 ft 6 in face, includes twelve 96 in pipes

## Product Classification

**Product Type**                      Monopole platform kit

## General Specifications

**Mounting**                              Monopole, 254–762 mm (10–30 in) OD

**Pipe, quantity**                      12

**Sectors, quantity**                      3

## Dimensions

**Height**                                  2,438.4 mm | 96 in

**Face Width**                          4.42 m | 14.5 ft

**Width**                                  4,419.6 mm | 174 in

**Pipe Length**                          2,438.4 mm | 96 in

**Mounting Diameter, maximum**      762 mm | 30 in

**Mounting Diameter, minimum**      254 mm | 10 in

**Pipe Outer Diameter**                  60.96 mm | 2.4 in

## Material Specifications

**Material Type**                      Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating**                      120 mph (BWS) at 100 ft AGL | 140 mph (3-second gust) at 150 ft AGL using Exposure D per FBC

# MC-CP14S-12-96

---

Wind Rating Test Method	TIA/EIA-222
Packaging and Weights	
Included	Plain end pipes (12)   Platform   Rail   Ring mount
Packaging quantity	1
Weight, net	884.959 kg   1951 lb

\* Footnotes

Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code
-------------	--