


# CLT-CAPKIT

---



End Cap Assembly for MQ male port, work torque 5N/M

## Product Classification

<b>Product Type</b>	Wireless and radiating connector
<b>Product Brand</b>	HELIAX®

## Dimensions

<b>Length</b>	11 mm   0.433 in
<b>Diameter</b>	36 mm   1.417 in

## Mechanical Specifications

<b>Coupling Nut Proof Torque</b>	5 N-m   44.254 in lb
<b>Mechanical Shock Test Method</b>	IEC 60068-2-27

## Environmental Specifications

<b>Operating Temperature</b>	-55 °C to +85 °C (-67 °F to +185 °F)
<b>Storage Temperature</b>	-65 °C to +125 °C (-85 °F to +257 °F)
<b>Attenuation, Ambient Temperature</b>	20 °C   68 °F
<b>Average Power, Ambient Temperature</b>	40 °C   104 °F
<b>Average Power, Inner Conductor Temperature</b>	100 °C   212 °F
<b>Corrosion Test Method</b>	IEC 60068-2-11
<b>Immersion Depth</b>	1 m
<b>Immersion Test Mating</b>	Mated
<b>Immersion Test Method</b>	IEC 60529:2001, IP68
<b>Moisture Resistance Test Method</b>	IEC 60068-2-3
<b>Thermal Shock Test Method</b>	IEC 60068-2-14

# CLT-CAPKIT

---

**Vibration Test Method** IEC 60068-2-6

## Packaging and Weights

**Weight, net** 5.21 g | 0.011 lb

## \* Footnotes

**Immersion Depth** Immersion at specified depth for 24 hours