SP-10400L1L1CBAA | PLC 1X4 900UM IN/OUT LC /UPC GRADE C



Wideband PLC Splitter, singlemode, 1x4, symmetrical split ratio, 0.900 mm cable, LC/UPC grade C

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | EMEA | India | Latin

America | North America

Product Type Bare splitter

General Specifications

Device Type Component, rectangular

Functionality Splitting

Technology Type Planar lightwave circuit (PLC)

Distribution Type 1 x 4 splitter

Interface, Input LC/UPC

Interface, Output LC/UPC

Split Ratio Symmetrical

Splitter, quantity 1

Dimensions

Height 4 mm | 0.157 in

Width 7 mm | 0.276 in

Length 60 mm | 2.362 in

 $\label{eq:pigtail Length, Input} \mbox{1 m} \ | \ 3.281 \ \mbox{ft}$

 $\label{eq:pigtail} \textbf{Pigtail Length, Output} \hspace{1cm} 1 \text{ m} \hspace{0.1cm} \mid \hspace{0.1cm} 3.281 \text{ ft}$

Pigtail Diameter, Input 0.9 mm | 0.035 in

Pigtail Diameter, Output 0.9 mm | 0.035 in

Optical Specifications

Fiber Type G.657.A2 **Directivity, minimum** 55 dB

COMMSC PE°

SP-10400L1L1CBAA | PLC 1X4 900UM IN/OUT LC /UPC GRADE C

Polarization Dependent Loss, maximum 0.2 dB

Uniformity, maximum 1 dB

Wavelength Range 1260–1650 nm

Insertion Loss, Splitter, maximum7.7 dBReturn Loss, Splitter, minimum50 dB

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to} + 158 \,^{\circ}\text{F})$

Relative Humidity 5%–95%, non-condensing

Packaging and Weights

Packaging quantity 1

