


# SP-11600L2L2CAAA | PLC 1x16 250UM IN/OUT LC /APC GRADE C



Wideband PLC Splitter, singlemode, 1x16, symmetrical split ratio, 0.250 mm cable, LC/APC grade C

## Product Classification

### Regional Availability

Asia | Australia/New Zealand | China | EMEA | India | Latin America | North America

### Product Type

Bare splitter

## General Specifications

### Device Type

Component, rectangular

### Functionality

Splitting

### Technology Type

Planar lightwave circuit (PLC)

### Distribution Type

1 x 16 splitter

### Interface, Input

LC

### Interface, Output

LC

### Interface Feature, Output

APC

### Split Ratio

Symmetrical

### Splitter, quantity

1

## Dimensions

### Height

4 mm | 0.157 in

### Width

5 mm | 0.197 in

### Length

45 mm | 1.772 in

### Pigtail Length, Input

1 m | 3.281 ft

### Pigtail Length, Output

1 m | 3.281 ft

### Pigtail Diameter, Input

0.25 mm | 0.01 in

### Pigtail Diameter, Output

0.25 mm | 0.01 in

## Optical Specifications

### Fiber Type

G.657.A2

# SP-11600L2L2CAAA | PLC 1X16 250UM IN/OUT LC /APC GRADE C

---

<b>Directivity, minimum</b>	55 dB
<b>Polarization Dependent Loss, maximum</b>	0.3 dB
<b>Uniformity, maximum</b>	1.6 dB
<b>Wavelength Range</b>	1260–1650 nm
<b>Insertion Loss, Splitter, maximum</b>	14.3 dB
<b>Return Loss, Splitter, minimum</b>	50 dB

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Relative Humidity</b>	5%–95%, non-condensing

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---