## 810010142/DB | B-002-CN-8W-M02BK/20G



Fiber OSP cable, LightScope® ZWP Blown Single Jacket All-Dielectric 2fiber, Central Tube Construction, Singlemode G.657.A1, Gel-filled, Meters jacket marking, Black jacket color

### Product Classification

Regional Availability	Europe
Portfolio	CommScope®
Product Type	Fiber OSP cable
Product Series	B-CN
General Specifications	
Cable Type	Central tube, all dielectric   Microcable
Construction Type	Non-armored
Subunit Type	Gel-filled
Filler, quantity	0
Inner Jacket Color	White
Jacket Color	Black
Jacket Marking	Meters
Jacket Marking Method	Inkjet
Jacket Marking Text	COMMSCOPE GB OPTICAL CABLE 810010142/DB 2x G657A1 SM [SERIAL NUMBER] [METER MARK]
Subunit, quantity	1
Fibers per Subunit, quantity	2
Total Fiber Count	2
Dimensions	
Buffer Tube/Subunit Diameter	2 mm   0.079 in
Diameter Over Jacket	2.5 mm   0.098 in


### Representative Image

Page 1 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 24, 2025



## 810010142/DB | B-002-CN-8W-M02BK/20G



Material Specifications	
Jacket Material	Nylon
Mechanical Specifications	
Minimum Bend Radius, loaded	30 mm   1.181 in
Minimum Bend Radius, storage coils	30 mm   1.181 in
Minimum Bend Radius, unloaded	30 mm   1.181 in
Tensile Load, long term, maximum	75 N   16.861 lbf
Compression	10 N/mm   57.101 lb/in
Compression Test Method	IEC 60794-1-21 E3
Flex	25 cycles
Impact	2 N-m   17.701 in lb
Impact Test Method	IEC 60794-1-21 E4
Strain	See long and short term tensile loads
Strain Test Method	IEC 60794-1-21 E1
Twist	10 cycles
Twist Test Method	IEC 60794-1-21 E7

### **Optical Specifications**

Fiber Type

G.652.D and G.657.A1

Page 2 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 24, 2025



# 810010142/DB | B-002-CN-8W-M02BK/20G

#### **Environmental Specifications**

Installation temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Storage Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Cable Qualification Standards	IEC 60794-1-2   IEC 60794-5-10
Environmental Space	Air-blown, microduct
Jacket UV Resistance	UV stabilized
Water Penetration	24 h
Water Penetration Test Method	IEC 60794-1 F5

#### **Environmental Test Specifications**

Low High Bend Test Method	IEC 60794-1-21 E11
Temperature Cycle	-20 °C to +60 °C (-4 °F to +140 °F)
Temperature Cycle Test Method	IEC 60794-1-22 F1
Packaging and Weights	

#### Cable weight

6.1 kg/km | 4.099 lb/kft

#### Included Products

CS-8W-250-EMEA – LightScope® ZWP Singlemode Fiber 8W-250um

### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 24, 2025

