U4GLALACH

Base Product



Ultra Low Loss ULL TeraSPEED® LC/APC to LC/APC Ruggedized fanout Cable, 48-Fiber, LSZH, 12 fiber PmP 2.0 mm /B2ca

Product Classification

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle

East/Africa | North America

Portfolio CommScope®

Product Type Ruggedized fanout

Product Brand SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales

Representative | For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may vary based on cable configuration

General Specifications

Color, boot A Green

Color, connector A Green

Color, boot B Green

Color, connector B Green

Construction Type Stranded

Furcation Color Yellow

Interface, Connector A LC/APC

Interface Feature, connector A ULL

Interface, Connector B LC/APC

Interface Feature, connector B ULL

Jacket Color Yellow

Fibers per Subunit, quantity 12

Total Fibers, quantity 48

Dimensions

Cable Assembly Length Range (m) 3 - 999
Cable Assembly Length Range (ft) 8 - 999

Page 1 of 5

U4GLALACH

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A2, TeraSPEED®

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

EN50575 CPR Cable EuroClass Fire Performance B2ca

Environmental Space Indoor | Low Smoke Zero Halogen (LSZH)

Regulatory Compliance/Certifications

Agency Classification
ANATEL Compliant

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



Included Products

760249608 – Fiber indoor cable, Low Smoke Zero Halogen Riser MPO Trunk, 48 fiber with 2.0 mm Subunits, N-048-MP-8G1-F12YL/20T/B2 Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color, B2ca flame rating



760249608 | N-048-MP-8G1-F12YL/20T/B2



Fiber indoor cable, Low Smoke Zero Halogen Riser MPO Trunk, 48 fiber with 2.0 mm Subunits, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color, B2ca flame rating

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA

 Portfolio
 CommScope®

 Product Type
 Fiber indoor cable

Product Series N-MP

General Specifications

Cable TypeMPO trunk cableConstruction TypeNon-armoredSubunit TypeGel-freeJacket ColorYellowJacket MarkingFeet

Subunit, quantity 4

Fibers per Subunit, quantity 12

Total Fiber Count 48


Dimensions

Buffer Tube/Subunit Diameter2 mm | 0.079 inDiameter Over Jacket7.8 mm | 0.307 in

Representative Image



760249608 | N-048-MP-8G1-F12YL/20T/B2



Mechanical Specifications

Minimum Bend Radius, loaded 116 mm | 4.567 in

Minimum Bend Radius, unloaded 78 mm | 3.071 in

Tensile Load, long term, maximum 200 N | 44.962 lbf

Tensile Load, short term, maximum 667 N | 149.948 lbf

Compression 10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 336 m | 1,102.362 ft

Optical Specifications

Fiber Type G.657.A2/B2 | OS2

Environmental Specifications

Installation temperature $0 \,^{\circ}\text{C}$ to +50 $^{\circ}\text{C}$ (+32 $^{\circ}\text{F}$ to +122 $^{\circ}\text{F}$)

Operating Temperature $0 \,^{\circ}\text{C}$ to +60 $^{\circ}\text{C}$ (+32 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)



760249608 | N-048-MP-8G1-F12YL/20T/B2

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

EN50575 CPR Cable EuroClass Fire PerformanceB2caEN50575 CPR Cable EuroClass Smoke Ratings1aEN50575 CPR Cable EuroClass Droplets Ratingd0

EN50575 CPR Cable EuroClass Acidity Rating a1

Environmental Space Low Smoke Zero Halogen (LSZH)

Flame Test Method IEC 60332-3 | IEC 60754-2 | IEC 61034-2

Environmental Test Specifications

Low High Bend $0 \,^{\circ}\text{C}$ to +70 $^{\circ}\text{C}$ (+32 $^{\circ}\text{F}$ to +158 $^{\circ}\text{F}$) **Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

Temperature Cycle 0 °C to +70 °C (+32 °F to +158 °F)

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 60.8 kg/km | 40.856 lb/kft

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

