



Outside Plant Fiber Optic Cable, HDPE, 8-fiber, Multimode, OM3, loose tube, gel-filled, 1000 m

## Product Classification

<b>Regional Availability</b>	Australia/New Zealand   EMEA
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber OSP cable
<b>Product Series</b>	O-CA

## General Specifications

<b>Armor Type</b>	Corrugated steel
<b>Cable Type</b>	Loose tube
<b>Subunit Type</b>	Gel-filled
<b>Jacket Color</b>	Black
<b>Jacket Marking</b>	Meters
<b>Jacket Marking Method</b>	Inkjet
<b>Jacket Marking Text</b>	COMMSCOPE GB SYSTEM F.O. CABLE X-599692-3 CSA GEL LOOSE TUBE 8X50/125 OM3 HDPE (Serial NUMBER) (METRE MARK)
<b>Fibers per Subunit, quantity</b>	8
<b>Total Fiber Count</b>	8

## Dimensions

<b>Cable Length</b>	1000 m   3,280.84 ft
<b>Diameter Over Jacket</b>	10 mm   0.394 in

## Material Specifications

<b>Jacket Material</b>	High density polyethylene (HDPE)
------------------------	----------------------------------

## Mechanical Specifications

<b>Minimum Bend Radius, loaded</b>	200.7 mm   7.902 in
<b>Minimum Bend Radius, unloaded</b>	160 mm   6.299 in

# 1-599692-3 | 0-008-CA-5L-M08BK/28G/HD/1K

**Tensile Load, long term, maximum** 1250 N | 281.011 lbf

**Flex** 25 cycles

## Optical Specifications

**Fiber Type** OM3

## Optical Specifications, Wavelength Specific

**Attenuation, maximum** 0.70 dB/km @ 1,300 nm | 3.50 dB/km @ 850 nm

**Standards Compliance** TIA-492AAAC (OM3)

## Environmental Specifications

**Installation temperature** -5 °C to +50 °C (+23 °F to +122 °F)

**Operating Temperature** -20 °C to +70 °C (-4 °F to +158 °F)

**Storage Temperature** -20 °C to +70 °C (-4 °F to +158 °F)

## Packaging and Weights

**Cable weight** 104 kg/km | 69.885 lb/kft

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## Included Products

CS-5L-TB – LazrSPEED® 300 OM3 Bend-Insensitive Multimode Fiber

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable