

760254866 | PPL-DM-NULL-8APLC-SM-BEU



Propel ULL Singlemode MPO-08 front facing breakout module, 4 duplex LC/UPC to 1X8f MPO/APC pinned, Method B Enhanced

- Ultra-low loss (ULL) with Method B Enhanced polarity
- Can be installed and removed from front or rear of panel
- Serialized QR code provides easy access to factory optical test results
- This component requires 3 of the 12 lanes on the Propel Panel blade

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | SYSTIMAX® |
| Product Type | Fiber module |
| Product Brand | Propel |
| Product Series | PPL |

General Specifications

| | |
|-------------------------------------|--|
| Functionality | Breakout |
| Color, front | Blue Gray |
| Interface, front | LC/UPC + MPO |
| Interface Feature, front | Internal shutters MPO Pinned MPO/APC |
| Polarity | Method B Enhanced (ULL) |
| Total Fibers, quantity | 8 |
| Total Ports, quantity, front | 5 |
| Total Ports, quantity, rear | 0 |

Dimensions

| | |
|---------------|-------------------|
| Height | 11 mm 0.433 in |
| Width | 98 mm 3.858 in |
| Depth | 170 mm 6.693 in |

Optical Specifications

| | |
|--------------------------------|------------|
| Fiber Mode | Singlemode |
| Fiber Type | OS2 |
| Insertion Loss, maximum | 0.6 dB |

Environmental Specifications

Qualification Standards IEC 61753-1 | TIA-568.3-D

Safety Standard UL 62368

Packaging and Weights

Packaging quantity 1