UJGMXUCSF

Base Product



Ultra Low Loss (ULL) Singlemode MPO12 (Pinned) to Unconnectorized, Fiber Trunk Cable Assembly, 24-Fiber, Dual Rated LSZH/Riser Cca

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

Product Type Fiber trunk cable assembly

Product Brand SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

General Specifications

Color, boot A Black
Color, connector A Green

Construction Type Rollable ribbon

Furcation Color Yellow

Interface, Connector A MPO-12/APC Male

Jacket Color Black

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 12

Total Fibers, quantity 24

Dimensions

Breakout Length 33 in


Cable Assembly Length Range (m) 3 - 999

Cable Assembly Length Range (ft) 10 - 999

Ordering Tree



UJGMXUCSF



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A2, TeraSPEED®

Environmental Specifications

-10 °C to +60 °C (+14 °F to +140 °F) **Operating Temperature**

Environmental Space Dual Rated LSZH/Riser | Indoor/Outdoor

Included Products

Fiber indoor/outdoor cable, OFNR/LSZH Riser Rollable Ribbon Dual Rated Backbone, 24 fiber, 760256411 Z-024-MP-RR-F12BK/8G1/99N /C

Singlemode G.657.A2/B2, Feet jacket marking, Black jacket color, Cca flame rating

MPO12, ULTRA LOW LOSS, MALE, Singlemode, GREEN, 3mm 860638317

760256411 | Z-024-MP-RR-F12BK/8G1/99N/C



Fiber indoor/outdoor cable, OFNR/LSZH Riser Rollable Ribbon Dual Rated Backbone, 24 fiber, Singlemode G.657.A2/B2, Feet jacket marking, Black jacket color, Cca flame rating

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

Portfolio CommScope®

Product Type Fiber indoor/outdoor cable

Product Series N-MP

General Specifications

 Cable Type
 Riser rated low smoke

Construction Type Non-armored

Subunit Type Gel-free

Fibers per Ribbon, quantity 12

Jacket Color Black

Jacket Marking Feet

Total Fiber Count 24


Dimensions

Diameter Over Jacket 5.8 mm | 0.228 in

Representative Image



760256411 | Z-024-MP-RR-F12BK/8G1/99N/C



Mechanical Specifications

Minimum Bend Radius, loaded 116 mm | 4.567 in

Minimum Bend Radius, unloaded46 mm | 1.811 inTensile Load, long term, maximum198 N | 44.512 lbf

Tensile Load, short term, maximum 660 N | 148.374 lbf

Compression 10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Optical Specifications

Fiber Type G.657.A2/B2 | G.657.A2/B2

Environmental Specifications

Installation temperature $-30 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-22 $^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

COMMSCOPE®

760256411 | Z-024-MP-RR-F12BK/8G1/99N/C

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Cable Qualification Standards ANSI/ICEA S-104-696 | Telcordia GR-409

EN50575 CPR Cable EuroClass Fire PerformanceCcaEN50575 CPR Cable EuroClass Smoke Ratings1aEN50575 CPR Cable EuroClass Droplets Ratingd1EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Low Smoke Zero Halogen (LSZH) | Riser

Flame Test Listing NEC OFNR (UL) and c(UL)

Flame Test Method FT4 | UL 1666

Environmental Test Specifications

Heat Age $0 \, ^{\circ}\text{C to} + 85 \, ^{\circ}\text{C} \, (+32 \, ^{\circ}\text{F to} + 185 \, ^{\circ}\text{F})$

Heat Age Test Method IEC 60794-1 F9

Low High Bend -10 °C to +60 °C (+14 °F to +140 °F)

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle -20 °C to +70 °C (-4 °F to +158 °F)

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 34.6 kg/km | 23.25 lb/kft

Regulatory Compliance/Certifications

Agency Classification ANATEL Compliant

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable





MPO12, ULTRA LOW LOSS, MALE, Singlemode, GREEN, 3mm

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

 Portfolio
 CommScope®

 Product Type
 Fiber connector

 Product Brand
 TeraSPEED®

General Specifications

ColorGreenColor, bootBlackFerrule GeometryAngled

Interface MPO/APC Male

Interface FeaturePinnedTotal Fiber Count12

Dimensions

Length 60.1 mm | 2.366 in Compatible Cable Diameter 3 mm | 0.118 in

Material Specifications

Ferrule Material Polymer

Mechanical Specifications

Cable Retention Strength, maximum $11.24 \text{ lb} @ 0 \degree$ Mechanical Components StandardIEC 61754-7

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.652.D and G.657.A1, TeraSPEED® | OS2

Insertion Loss Change, mating 0.3 dB

Page 6 of 7

860638317

Optical Components Standard ANSI/TIA-568-C.3

Insertion Loss Change, temperature0.3 dBInsertion Loss, maximum0.35 dBReturn Loss, minimum65 dB

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



* Footnotes

Insertion Loss Change, matingTIA-568: Maximum insertion loss change after 500 matings

Insertion Loss Change, temperature Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)

