

HST, NOVUX™ Prodigy™ Hardened Standard Terminal, 4-port Planar 1:4 Splitter, Dielectric flat loose tube cable, 1000 ft/304 m, Universal mounting bracket

- NOVUX™ Prodigy™ Hardened Multi-port Terminals incorporate Hardened connector technology that is designed to withstand the rugged outside plant environment
- Hardened connectors are factory-integrated and environmentally sealed for use in optical drop cable deployments
- Plug and play adapter ports ensure rapid cable installment in the outside plant access section of the network
- NOVUX™ Prodigy™ HST terminals are available with 2 to 12 ports and can be utilized in Single Fiber Point-to-Point (P2P) solutions
- Available with flat dielectric, flat toneable/locatable dielectric, armored or 5mm round cable
- NOVUX<sup>™</sup> Prodigy<sup>™</sup> smaller terminal size for aesthetics and allowing installation in constrained spaces
- NOVUX™ Prodigy™ terminals are available in Black (RAL# 9005) or Gray (RAL# 7035)
- CommScope Product ID plate with QR code link to product documents and C-Track
- \*CommScope intends to release this product at a future date. At such time, this product will
  comply with the requirements of the Build America, Buy America Act and/or applicable waivers.
   Compliance requirements and waiver applicability vary based on government funding program.
   Check the laws and regulations for your specific program.
- \*Product as currently available does not comply with the requirements of the Build America, Buy America Act. A new version under the same product number meeting the requirements listed above will be available at a future date.

#### **Product Classification**

Regional Availability

Asia | EMEA | Latin America | North America

**Product Type** Access terminal, with splitter/tap

Product Brand NOVUX™
Product Series HST

Government Requirements Build America Buy America (BABA) coming soon\*

Minimum Order Quantity

General Specifications

Cable Type Dielectric - Flat - Loose Tube

Cable, quantity

**Distribution Type** 1 x 4 splitter

**Drop Port Type**Hardened Prodigy SC/APC

Drop Port, quantity

Page 1 of 4



**Enclosure Color** Black (RAL 9005)

**Location of Manufacturing** Coming soon

Mounting Handhole | Pedestal | Pole | Strand

Port Type Hardened Prodigy SC/APC

Port, quantity 4
Splitter, quantity 1

Stub Type Stub tail

**Dimensions** 

 Height
 80 mm | 3.15 in


 Width
 79 mm | 3.11 in


 Length
 161 mm | 6.339 in

 Cable Length, stub
 1000 ft (304 m)

**Cable Outer Diameter** 4.3 x 8.0 mm (0.17 x 0.31 in)

### Dimension Drawing








### Port Configuration

| NOVUXHT    | TECHNOLOGIES AVAILABLE         | SMALL                          | MEDIUM                         | LARGE  |
|------------|--------------------------------|--------------------------------|--------------------------------|--|
| HST Series | Single-fiber: P2P/no splitters | 2 ports                        | 6 ports                        | 12 ports                                       |
|            |                                | 4 ports                        | 8 ports                        |  |
|            | Single-fiber: P2P w/splitters  | 2 ports, 1x1:2                 | 8 ports, 2x1:4                 | 12 ports, 3x1:4                                |
|            |                                | 4 ports, 1x1:4                 | 8 ports, 1x1:8                 |  |
|            | Hybrid for multi-use           |                                | 7 ports, 1x1:4 splitter, 3 P2P | 12 ports, 1x1:8 splitter, 4 P2P                |
|            |                                | 4 ports, 1x1:2 splitter, 2 P2P | 8 ports, 1x1:4 splitter, 4 P2P | 11 ports, 2x1:4 splitter, 2 P2P,<br>1 HMFOC 4f |

#### Ordering Tree



### Material Specifications

Enclosure Material Type Hardened plastic

Optical Specifications

**Fiber Type** G.657.A1/A2

**Operating Wavelength Range** 1260 – 1635 nm

Attenuation Single Ports, maximum 7.5 dB

**COMMSCOPE®** 

**Attenuation Cable Coefficient, maximum** 0.30 dB/km @ 1550 nm | 0.40 dB/km @ 1310 nm

7.1 dB Attenuation Splitter, maximum **Attenuation Terminal Connectors, maximum** 0.4 dB Return Loss, Single Ports, minimum 55 dB

#### **Environmental Specifications**

**Operating Temperature** -40 °C to +65 °C (-40 °F to +149 °F)

**Relative Humidity** 5%-100%, condensing

**Environmental Space** Above ground | Below ground

IEC 61753-1, category G | IEC 61753-111-08 (this represents an IEC 60529 **Oualification Standards** 

IP68 intrusion protection level)

**UV Resistance** UV stabilized

Packaging and Weights

Included Universal mounting bracket

1 Packaging quantity

Box | Universal spool, cardboard: terminal is on top of the spool, stub deploys **Packaging Type** 

#### Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC    | Compliant as per SVHC revision on www.commscope.com/ProductCompliance          |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |

