## 760255941 | C-008-DS-5X-MSUBL



Fiber indoor/outdoor cable, LSZH Riser Distribution, 8 fiber single-unit, Multimode OM4 bend insensitive, Meters jacket marking, Blue jacket color

## **Product Classification**

Regional Availability Asia | Australia/New Zealand

Portfolio CommScope®

**Product Type** Fiber indoor/outdoor cable

**Product Series** C-DS

General Specifications

Cable TypeTight buffer

Jacket Color Blue

Jacket Marking Meters

**Strength Members** E-glass yarns

Total Fiber Count 8

**Dimensions** 

**Diameter Over Jacket** 5.4 mm | 0.213 in

Material Specifications

Jacket MaterialLow Smoke Zero Halogen (LSZH)Inner Jacket MaterialLow Smoke Zero Halogen (LSZH)

Mechanical Specifications

Minimum Bend Radius, loaded 108 mm | 4.252 in

Minimum Bend Radius, unloaded 54 mm | 2.126 in

**Tensile Load, short term, maximum** 600 N | 134.885 lbf

**Compression** 5 N/mm | 28.551 lb/in

**Compression Test Method** IEC 60794-1-21 E3

**Impact** 1 N-m | 8.851 in lb

Impact Test Method IEC 60794-1-21 E4

Strain Test Method IEC 60794-1-21 E1



## 760255941 | C-008-DS-5X-MSUBL

Twist 10 cycles

Twist Test Method IEC 60794-1-21 E7

**Optical Specifications** 

**Fiber Type** OM4, bend insensitive

Optical Specifications, Wavelength Specific

**Attenuation, maximum** 1.00 dB/km @ 1,300 nm | 3.00 dB/km @ 850 nm

**Environmental Specifications** 

**Installation temperature** 0 °C to +50 °C (+32 °F to +122 °F)

**Operating Temperature**  $-10 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \text{ (+14 }^{\circ}\text{F to } +158 \,^{\circ}\text{F)}$ 

Storage Temperature  $-10 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (+14  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )

**Environmental Space** Low Smoke Zero Halogen (LSZH)

Flame Test Method IEC 60332-3-24

Jacket UV Resistance UV stabilized

Water Penentration 24 h

**Water Penentration Test Method** IEC 60794-1 F5C

**Environmental Test Specifications** 

**Temperature Cycle Test Method** IEC 60794-1-22 F1

Packaging and Weights

Cable weight 26 kg/km | 17.471 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



\* Footnotes



## 760255941 | C-008-DS-5X-MSUBL

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable