

Fiber outdoor drop cable, LightScope® ZWP Self-Supporting All-Dielectric, Singlemode G.652.D and G.657.A1, 4 fiber Arid Core construction, Gel-filled, central loose tube, Feet jacket marking, Black jacket color, 2000 ft

- \*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber drop cable
Product Series	O-DF
Government Requirements	Build America Buy America (BABA) compliant*

General Specifications


Cable Type	Central loose tube
Construction Type	Non-armored
Subunit Type	Gel-filled
Jacket Color	Black
Jacket Marking	Feet
Location of Manufacturing	Catawba, North Carolina
Subunit, quantity	1
Fibers per Subunit, quantity	4
Total Fiber Count	4

Dimensions

Height Over Jacket	4.5 mm   0.177 in
Cable Length	609.6 m   2000 ft
Buffer Tube/Subunit Diameter	3 mm   0.118 in

Diameter Over Jacket7.9 mm | 0.311 in

Representative Image



Material Specifications

Jacket MaterialPE

Mechanical Specifications

Minimum Bend Radius, loaded	86 mm   3.386 in
Minimum Bend Radius, unloaded	81 mm   3.189 in
Tensile Load, long term, maximum	400 N   89.924 lbf
Tensile Load, short term, maximum	1334 N   299.895 lbf
Compression	10 N/mm   57.101 lb/in
Compression Test Method	FOTP-41   IEC 60794-1 E3
Flex	35 cycles
Flex Test Method	FOTP-104   IEC 60794-1 E6
Impact	2.94 N-m   26.021 in lb
Impact Test Method	FOTP-25   IEC 60794-1 E4
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33   IEC 60794-1 E1
Twist	10 cycles
Twist Test Method	FOTP-85   IEC 60794-1 E7

Vertical Rise, maximum1047 m | 3,435.039 ft

Optical Specifications

Fiber TypeG.652.D and G.657.A1 | G.652.D and G.657.A1

Environmental Specifications

Installation temperature-30 °C to +70 °C (-22 °F to +158 °F)

Operating Temperature-40 °C to +70 °C (-40 °F to +158 °F)

Storage Temperature-40 °C to +75 °C (-40 °F to +167 °F)

Cable Qualification StandardsANSI/ICEA S-110-717 | Telcordia GR-20

Environmental SpaceAerial, self-support | Buried

Jacket UV ResistanceUV stabilized

Water Penetration24 h

Water Penetration Test MethodFOTP-82 | IEC 60794-1 F5

Environmental Test Specifications

Cable Freeze-2 °C | 28.4 °F

Cable Freeze Test MethodFOTP-98 | IEC 60794-1 F15

Drip70 °C | 158 °F

Drip Test MethodFOTP-81 | IEC 60794-1 E14

Heat Age-40 °C to +85 °C (-40 °F to +185 °F)

Heat Age Test MethodIEC 60794-1 F9

Low High Bend-30 °C to +60 °C (-22 °F to +140 °F)

Low High Bend Test MethodFOTP-37 | IEC 60794-1 E11

Temperature Cycle-40 °C to +70 °C (-40 °F to +158 °F)

Temperature Cycle Test MethodFOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight39 kg/km | 26.207 lb/kft

Included Products

DB-8W-LT – LightScope® ZWP Singlemode Fiber

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable