

Fiber outdoor drop cable, LightScope® ZWP Self-Supporting All-Dielectric, Singlemode G.652.D and G.657.Al, 12 fiber Arid Core construction, Gel-filled, central loose tube, Feet jacket marking, Black jacket color, 5000 ft

 *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

 Portfolio
 CommScope®

 Product Type
 Fiber drop cable

Product Series O-DF

Government Requirements Build America Buy America (BABA) compliant*

General Specifications

Cable Type Central loose tube

Construction Type Non-armored

Subunit TypeGel-filledJacket ColorBlackJacket MarkingFeet

Location of ManufacturingCatawba, North Carolina

Subunit, quantity 1
Fibers per Subunit, quantity 12
Total Fiber Count 12

Dimensions

 Height Over Jacket
 4.5 mm | 0.177 in

 Cable Length
 1,524 m | 5000 ft

 Buffer Tube/Subunit Diameter
 3 mm | 0.118 in


Page 1 of 4



Diameter Over Jacket

7.9 mm | 0.311 in

Representative Image



Material Specifications

Jacket Material PE

Mechanical Specifications

Minimum Bend Radius, loaded86 mm | 3.386 inMinimum Bend Radius, unloaded81 mm | 3.189 inTensile Load, long term, maximum400 N | 89.924 lbfTensile Load, short term, maximum1334 N | 299.895 lbfCompression10 N/mm | 57.101 lb/inCompression Test MethodFOTP-41 | IEC 60794-1 E3

Flex 35 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

COMMSCOPE®

Vertical Rise, maximum 1047 m | 3,435.039 ft

Optical Specifications

Fiber Type G.652.D and G.657.A1 | G.652.D and G.657.A1

Environmental Specifications

Installation temperature $-30 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-22 °F to +158 °F)

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 °F to +158 °F)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+75 \,^{\circ}\text{C}$ (-40 °F to +167 °F)

Cable Qualification StandardsANSI/ICEA S-110-717| Telcordia GR-20

Environmental Space Aerial, self-support | Buried

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Test Method FOTP-82 | IEC 60794-1 F5

Environmental Test Specifications

Cable Freeze -2 °C | 28.4 °F

Cable Freeze Test Method FOTP-98 | IEC 60794-1 F15

Drip 70 °C | 158 °F

Drip Test Method FOTP-81 | IEC 60794-1 E14

Heat Age $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ $(-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$

Heat Age Test Method IEC 60794-1 F9

Low High Bend $-30 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-22 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 39 kg/km | 26.207 lb/kft

Included Products

DB-8W-LT - LightScope® ZWP Singlemode

Fiber



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable