

Fiber outdoor drop cable, LightScope® ZWP Self-Supporting All-Dielectric, Singlemode G.652.D and G.657.A1, 12 fiber Arid Core construction, Gel-filled, central loose tube, Feet jacket marking, Black jacket color, 5000 ft

- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber drop cable
Product Series	O-DF
Government Requirements	Build America Buy America (BABA) compliant*

General Specifications

Cable Type	Central loose tube
Construction Type	Non-armored
Subunit Type	Gel-filled
Jacket Color	Black
Jacket Marking	Feet
Location of Manufacturing	Catawba, North Carolina
Subunit, quantity	1
Fibers per Subunit, quantity	12
Total Fiber Count	12

Dimensions


Height Over Jacket	4.5 mm 0.177 in
Cable Length	1,524 m 5000 ft
Buffer Tube/Subunit Diameter	3 mm 0.118 in

810010250/50 | 0-012-DF-8W-F12NS (5000')

Diameter Over Jacket

7.9 mm | 0.311 in

Representative Image



Material Specifications

Jacket Material

PE

Mechanical Specifications

Minimum Bend Radius, loaded

86 mm | 3.386 in

Minimum Bend Radius, unloaded

81 mm | 3.189 in

Tensile Load, long term, maximum

400 N | 89.924 lbf

Tensile Load, short term, maximum

1334 N | 299.895 lbf

Compression

10 N/mm | 57.101 lb/in

Compression Test Method

FOTP-41 | IEC 60794-1 E3

Flex

35 cycles

Flex Test Method

FOTP-104 | IEC 60794-1 E6

Impact

2.94 N-m | 26.021 in lb

Impact Test Method

FOTP-25 | IEC 60794-1 E4

Strain

See long and short term tensile loads

Strain Test Method

FOTP-33 | IEC 60794-1 E1

Twist

10 cycles

Twist Test Method

FOTP-85 | IEC 60794-1 E7

810010250/50 | 0-012-DF-8W-F12NS (5000')

Vertical Rise, maximum 1047 m | 3,435.039 ft

Optical Specifications

Fiber Type G.652.D and G.657.A1 | G.652.D and G.657.A1

Environmental Specifications

Installation temperature -30 °C to +70 °C (-22 °F to +158 °F)

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Storage Temperature -40 °C to +75 °C (-40 °F to +167 °F)

Cable Qualification Standards ANSI/ICEA S-110-717

Environmental Space Aerial, self-support | Buried

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Test Method FOTP-82 | IEC 60794-1 F5

Environmental Test Specifications

Cable Freeze -2 °C | 28.4 °F

Cable Freeze Test Method FOTP-98 | IEC 60794-1 F15

Drip 70 °C | 158 °F

Drip Test Method FOTP-81 | IEC 60794-1 E14

Heat Age -40 °C to +85 °C (-40 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

Low High Bend -30 °C to +60 °C (-22 °F to +140 °F)

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle -40 °C to +70 °C (-40 °F to +158 °F)

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 39 kg/km | 26.207 lb/kft

Included Products

DB-8W-LT – LightScope® ZWP Singlemode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable