

HST, NOVUX[™] Prodigy[™] Hardened Standard Terminal, 4-port, Planar 1: 2 Splitter + two P2P, Dielectric flat loose tube cable, 1200 ft/365 m

- NOVUX[™] Prodigy[™] Hardened Multi-port Terminals incorporate Hardened connector technology that is designed to withstand the rugged outside plant environment
- Hardened connectors are factory-integrated and environmentally sealed for use in optical drop cable deployments
- Plug and play adapter ports ensure rapid cable installment in the outside plant access section of the network
- NOVUX[™] Prodigy[™] HST terminals are available with 2 to 12 ports and can be utilized in Single Fiber Point-to-Point (P2P) solutions
- Available with flat dielectric, flat toneable/locatable dielectric, armored or 5mm round cable
- NOVUX[™] Prodigy[™] smaller terminal size for aesthetics and allowing installation in constrained spaces
- NOVUX[™] Prodigy[™] terminals are available in Black (RAL# 9005) or Gray (RAL# 7035)
- CommScope Product ID plate with QR code link to product documents and C-Track

Product Classification

| Regional Availability | Asia EMEA Latin America North America |
|------------------------|---|
| Product Type | Access terminal, with splitter/tap |
| Product Brand | NOVUX™ |
| Product Series | HST |
| Minimum Order Quantity | 1 |
| General Specifications | |
| Cable Type | Dielectric - Flat - Loose Tube |
| Cable, quantity | 1 |
| Distribution Type | 1 x 2 splitter + P2P ports (2) |
| Drop Port Type | Hardened Prodigy SC/APC |
| Drop Port, quantity | 4 |
| Enclosure Color | Black (RAL 9005) |
| Mounting | Handhole Pedestal Pole Strand |
| Port Type | Hardened Prodigy SC/APC |
| Port, quantity | 4 |
| Splitter, quantity | 1 |
| Stub Type | Stub tail |


Page 1 of 4



Dimensions

| 80 mm 3.15 in |
|-------------------------------|
| 79 mm 3.11 in |
| 161 mm 6.339 in |
| 1200 ft (365 m) |
| 4.3 x 8.0 mm (0.17 x 0.31 in) |
| |

Dimension Drawing



Port Configuration


161 mm

| NOVUX HT | TECHNOLOGIES AVAILABLE | SMALL | MEDIUM | LARGE |
|------------|--------------------------------|--------------------------------|--------------------------------|--|
| HST Series | Single-fiber: P2P/no splitters | 2 ports | 6 ports | 12 ports |
| | | 4 ports | 8 ports | |
| | Single-fiber: P2P w/splitters | 2 ports, 1x1:2 | 8 ports, 2x1:4 | 12 ports, 3x1:4 |
| | | 4 ports, 1x1:4 | 8 ports, 1x1:8 | |
| | Hybrid for multi-use | | 7 ports, 1x1:4 splitter, 3 P2P | 12 ports, 1x1:8 splitter, 4 P2P |
| | | 4 ports, 1x1:2 splitter, 2 P2P | 8 ports, 1x1:4 splitter, 4 P2P | 11 ports, 2x1:4 splitter, 2 P2P, 1 HMFOC 4f |

Ordering Tree

Page 2 of 4





Material Specifications

| Enclosure Material Type | Hardened plastic |
|--|---|
| Optical Specifications | |
| Fiber Type | G.657.A1/A2 |
| Operating Wavelength Range | 1260 – 1635 nm |
| Attenuation Single Ports, maximum | 4.1 dB |
| Attenuation Cable Coefficient, maximum | 0.30 dB/km @ 1550 nm 0.40 dB/km @ 1310 nm |
| Attenuation Splitter, maximum | 3.7 dB |
| Attenuation Terminal Connectors, maximum | 0.4 dB |
| Return Loss, Single Ports, minimum | 55 dB |

Environmental Specifications

| Operating Temperature | -40 °C to +65 °C (-40 °F to +149 °F) |
|-----------------------|--------------------------------------|
| Relative Humidity | 5%–100%, condensing |

Page 3 of 4



Compliant

Compliant

REACH-SVHC

ROHS

UK-ROHS

| Environmental Space | Above ground Below ground | |
|--------------------------------------|--|---|
| Qualification Standards | | IEC 61753-1, category G IEC 61753-111-08 (this represents an IEC 60529 IP68 intrusion protection level) |
| UV Resistance | | UV stabilized |
| Packaging and Weights | | |
| Packaging quantity | | 1 |
| Packaging Type | | Box Universal spool, cardboard: terminal is on top of the spool, stub deploys first |
| Regulatory Compliance/Certifications | | |
| Agency | Classification | |
| CHINA-ROHS | Below maximum concentration value | |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system | |

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Page 4 of 4

