

TA-HFHF



4.3-10 Female to 4.3-10 Female Low-PIM Adapter

Product Classification

Product Type Adapter

General Specifications


Body Style	Straight
Inner Contact Plating	Silver
Interface	4.3-10 Female
Interface 2	4.3-10 Female
Mounting Angle	Straight
Outer Contact Plating	Trimetal

Dimensions

Length	36.8 mm 1.449 in
Diameter	20 mm 0.787 in

TA-HFHF

Outline Drawing



Electrical Specifications

3rd Order IMD at Frequency	-119 dBm @ 1900 MHz
3rd Order IMD Test Method	Two +43 dBm carriers
Connector Impedance	50 ohm
dc Test Voltage	2500 V
Inner Contact Resistance, maximum	1 mOhm
Insulation Resistance, minimum	5000 MOhm
Operating Frequency Band	0 – 6000 MHz
Outer Contact Resistance, maximum	1 mOhm

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
0-3000 MHz	1.052	32
3000-6000 MHz	1.106	26

Mechanical Specifications

Coupling Nut Proof Torque	8 N-m 70.806 in lb
Coupling Nut Retention Force	450 N 101.164 lbf
Interface Durability	100 cycles

TA-HFHF

Mechanical Shock Test Method	IEC 60068-2-27
Environmental Specifications	
Operating Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Storage Temperature	-65 °C to +125 °C (-85 °F to +257 °F)
Attenuation, Ambient Temperature	20 °C 68 °F
Average Power, Ambient Temperature	40 °C 104 °F
Average Power, Inner Conductor Temperature	100 °C 212 °F
Climatic Sequence Test Method	IEC 60068-1
Corrosion Test Method	IEC 60068-2-11
Damp Heat Steady State Test Method	IEC 60068-2-3
Immersion Depth	1 m
Immersion Test Mating	Mated
Immersion Test Method	IEC 60529:2001, IP68
Thermal Shock Test Method	IEC 60068-2-14
Vibration Test Method	IEC 60068-2-6

Packaging and Weights

Weight, net	40 g 0.088 lb
-------------	-----------------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Immersion Depth	Immersion at specified depth for 24 hours
-----------------	-------------------------------------------