


# 219413-2 | CS24CM WHT C5E 4/24 F/UTP RIB 305M



Copper Cable, category 5e, 4 pair, FTP, PVC, 24 AWG solid, 305 m reel-in-box, white

## Product Classification

|                              |                    |
|------------------------------|--------------------|
| <b>Regional Availability</b> | Asia   EMEA        |
| <b>Portfolio</b>             | CommScope®         |
| <b>Product Type</b>          | Twisted pair cable |

## General Specifications

|                                |   |
|--------------------------------|---|
| <b>ANSI/TIA Category</b>       | 5e  |
| <b>Cable Component Type</b>    | Horizontal  |
| <b>Cable Type</b>              | F/UTP (shielded)  |
| <b>Conductor Type, singles</b> | Solid   |
| <b>Conductors, quantity</b>    | 8   |
| <b>Jacket Color</b>            | White   |
| <b>Pairs, quantity</b>         | 4   |
| <b>Transmission Standards</b>  | ANSI/TIA-568.2-D   CENELEC EN 50288-3-1   ISO/IEC 11801 Class D |

## Dimensions

|                                      |                    |
|--------------------------------------|--------------------|
| <b>Cable Length</b>                  | 304.8 m   1000 ft  |
| <b>Diameter Over Jacket, nominal</b> | 6.096 mm   0.24 in |
| <b>Conductor Gauge, singles</b>      | 24 AWG             |

## Electrical Specifications

|                                   |   |
|-----------------------------------|---|
| <b>Operating Voltage, maximum</b> | 80 V  |
| <b>Remote Powering</b>            | Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A |

## Material Specifications

|                           |             |
|---------------------------|-------------|
| <b>Conductor Material</b> | Bare copper |
|---------------------------|-------------|

# 219413-2 | CS24CM WHT C5E 4/24 F/UTP RIB 305M

---

|                               |                    |
|-------------------------------|--------------------|
| <b>Insulation Material</b>    | Polyolefin         |
| <b>Jacket Material</b>        | PVC                |
| <b>Shield (Tape) Material</b> | Aluminum/Polyester |

## Environmental Specifications

|   |   |
|---|---|
| <b>Operating Temperature</b>                        | -20 °C to +60 °C (-4 °F to +140 °F)     |
| <b>EN50575 CPR Cable EuroClass Fire Performance</b> | Eca                                     |
| <b>Flame Test Method</b>                            | CM   NEC Article 800   UL 1685   UL 444 |

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CENELEC       | EN 50575 compliant, Declaration of Performance (DoP) available   |
| CHINA-ROHS    | Below maximum concentration value  |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |

