



- 1.0 GENERAL NOTES
 1.1 ALL IMPERIAL DIMENSIONS ARE IN BRACKETS [X.XX]
 1.2 MARK PART WITH IDENTIFICATION NUMBER
- 2.0 DESIGN NOTES
 2.1 DESIGNED PER CUSTOMER REQUIREMENTS
- 3.0 MANUFACTURING/SPECIAL REQUIREMENTS
 3.1 TIGHTEN ALL BOLTS SECURING FLAT PLATES BY THE TURN-OF-NUT METHOD. TIGHTEN ALL U-BOLTS USING TURN-OF-NUT METHOD WITH ATTENTION TO LEAVE EQUAL DISTANCE AND EQUAL FORCE ON EACH LEG OF THE U-BOLT.
- 4.0 TEST
- 5.0 PACKAGING
 5.1 PACKAGING SHALL MEET COMMSCOPE REQUIREMENTS PER DOCUMENT IS-PL-3005
 5.2 PRINTED DOCUMENT TO BE PLACED INSIDE POLYBAG AND THEN IN SHIPPING CONTAINER
 5.3 EXTRA HARDWARE MAYBE SUPPLIED, BAGGED AND SHIPPED

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	JL1183 01SEP22	VICENTE 40155958CMO



COMPONENT PART NUMBERS PROVIDED FOR ASSEMBLY PURPOSES;
 INDIVIDUAL COMPONENTS MAY BE SHIPPED AS PARTS WITHIN AN INCLUDED KIT.

ITEM NO.	PART NO.	DESCRIPTION	QTY.	NOTE NO.
1	CBP4-L	CORNER BENT PLATE BRACKET, LH	1	
2	CBP4-R	CORNER BENT PLATE BRACKET, RH	1	
3	GUB-53050	5/8" X 3" X 5" GALV U-BOLT KIT	4	INCLUDES U-BOLT, FLAT WASHERS, LOCK WASHERS AND NUTS
4	GB-0520A	5/8" X 2" GALV BOLT KIT (A325)	8	INCLUDED BOLT, LOCK WASHER AND NUT
5	GWF-05	5/8" GALV FLAT WASHER, 1.7OD	8	

DENSITY	0.29	lbs/in ³
MASS	26.93	lbs
VOLUME	95.04	in ³
SURFACE AREA	706.78	in ²
DENSITY	0.0079	g/mm ³
MASS	12238.8770	grams
VOLUME	1557575.2452	mm ³
SURFACE AREA	455988.8942	mm ²
HEIGHT	241[9.5]	
LENGTH	483[19.0]	
WIDTH	165[6.5]	

COMMSCOPE, INC. OF NORTH CAROLINA

TOLERANCES		SAP MATERIAL MASTER	
0 PLACE .X[.] ± 6[0.25]	2 PLACE .XX[.XXX] ± 1.50[0.06]	VZWSMART-PLK4	
1 PLACE .X[.XX] ± 3.0[0.12]	ANGLES ± 2°		
FINISH GALV A123		MATERIAL	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS INTERPRET PER ANSI Y 14.5M-1994		NAME	DATE
		CE JL1183	01SEP22
		RW JL1183	09/08/2022
		AD VCORTEZ1	09/14/2022
RE JL1183	09/15/2022	VZWSMART-PLK4	
ECN 40155958CMO			
SIZE	Auth Group	INSL	MODEL
A2		VERSION	STATUS
		00	RE
REVISION		VERSION	DRAWING
A		00	RE
A		A	
SHEET		1 OF 1	