

Fiber Optic Cable, Outdoor, Armored, Multimode, OM3 BIF, black

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber OSP cable
Product Series	O-LA
General Specifications	
Armor Type	Corrugated steel
Cable Type	Semi-tight buffer
Jacket Color	Black
Jacket Marking	Meters
Subunit Type	Gel-filled
Total Fiber Count	2
Dimensions	
Diameter Over Jacket	5.1 mm 0.201 in
Mechanical Specifications	
Minimum Bend Radius, loaded	50 mm 1.969 in
Tensile Load, long term, maximum	450 N 101.164 lbf
Tensile Load, short term, maximum	300 N 67.443 lbf
Cable Crush Resistance, maximum	50 N/mm 285.507 lb/in
Flex	25 cycles
Optical Specifications	

Fiber Type

OM3, bend insensitive

Page 1 of 2

©2022 CommScope, Inc. All rights reserved. All trademarks identified by ® or [™] are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: December 7, 2022



Optical Specifications, Wavelength Specific

Attenuation, maximum	0.60 dB/km @ 1,300 nm 2.20 dB/km @ 850 nm
Standards Compliance	TIA-492AAAC (OM3)

Environmental Specifications

Installation temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Environmental Space	Low Smoke Zero Halogen (LSZH)

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

Page 2 of 2

©2022 CommScope, Inc. All rights reserved. All trademarks identified by ® or [™] are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: December 7, 2022

