F1A-XMHM-8-P-W1



FSJ1-50A SureFlex® Jumper with interface types NEX10 Male and 4.3-10 Male with HELIAX® SureGuard weatherproofing boot on 4.3-10 side, 8 ft

WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type SureFlex® Premium, static PIM

Product Brand HELIAX® | SureFlex®

Product Series FSJ1-50A

General Specifications

Body Style, Connector AStraightBody Style, Connector BStraightInterface, Connector ANEX10 MaleInterface, Connector B4.3-10 Male

Specification Sheet Revision Level

Dimensions

Length 2.439 m | 8.002 ft

Nominal Size 1/4 in

Electrical Specifications

3rd Order IMD -116 dBm

3rd Order IMD Test Method Two +43 dBm carriers

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698-970 MHz	1.065	30
1700-2200 MHz	1.083	28
2500-2700 MHz	1.106	26
3400-3800 MHz	1.222	20

Jumper Assembly Sample Label



F1A-XMHM-8-P-W1



Environmental Specifications

Immersion Test MethodMeets IEC 60529:2001, IP68 in mated condition

Weatherproofing Method HELIAX® SureGuard weatherproofing boot

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

F1HM-S2 - 4.3-10 Male for 1/4 in foam coaxial cable, factory attached
F1XM-P-HS - NEX10 Male for 1/4 in foam coaxial cable, factory attached

FSJ1-50A - FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in,

black PE jacket



F1HM-S2

4.3-10 Male for 1/4 in foam coaxial cable, factory attached

Product Classification

Product Type Wireless and radiating connector

Product Brand HELIAX® | SureFlex®

General Specifications

Body StyleStraightInner Contact Attachment MethodSolderInner Contact PlatingSilver

Interface 4.3-10 Male

 Outer Contact Attachment Method
 Solder

 Outer Contact Plating
 Trimetal

Dimensions


 Length
 23.88 mm | 0.94 in

 Diameter
 23.88 mm | 0.94 in

Nominal Size 1/4 in

Outline Drawing





Electrical Specifications

3rd Order IMD at Frequency -119 dBm @ 910 MHz

3rd Order IMD Test Method Two +43 dBm carriers

Insertion Loss Coefficient, typical 0.05

Cable Impedance 50 ohm

Connector Impedance 50 ohm

dc Test Voltage 2300 V
Inner Contact Resistance, maximum 1 mOhm

Insulation Resistance, minimum 5000 MOhm

Operating Frequency Band 0 – 6000 MHz

Outer Contact Resistance, maximum 1 mOhm

Peak Power, maximum 6.4 kW

RF Operating Voltage, maximum (vrms) 565 V

VSWR/Return Loss

Frequency Band VSWR Return Loss (dB)

0–3000 MHz 1.041 33.94

COMMSCOPE®

F1HM-S2

3000–4000 MHz 1.065 30.04 **4000–6000 MHz** 1.119 25.01

Mechanical Specifications

Connector Retention Tensile Force449.27 N | 101 lbfConnector Retention Torque1.1 N-m | 9.736 in lbCoupling Nut Proof Torque8 N-m | 70.806 in lbCoupling Nut Retention Force449.98 N | 101.16 lbf

Interface Durability 100 cycles

Mechanical Shock Test Method IEC 60068-2-27

Environmental Specifications

Operating Temperature $-55 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-67 $^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Storage Temperature $-65 \,^{\circ}\text{C}$ to $+125 \,^{\circ}\text{C}$ (-85 $^{\circ}\text{F}$ to $+257 \,^{\circ}\text{F}$)

Attenuation, Ambient Temperature20 °C | 68 °FAverage Power, Ambient Temperature40 °C | 104 °FAverage Power, Inner Conductor Temperature100 °C | 212 °FCorrosion Test MethodIEC 60068-2-11

Immersion Depth1 mImmersion Test MatingMated

Immersion Test Method IEC 60529:2001, IP68

Moisture Resistance Test Method IEC 60068-2-3

Thermal Shock Test Method IEC 60068-2-14

Vibration Test Method IEC 60068-2-6

Packaging and Weights

Weight, net 31.21 g | 0.069 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant



F1HM-S2

UK-ROHS

Compliant/Exempted



* Footnotes

Insertion Loss Coefficient, typical 0.05√ freq (GHz) (not applicable for elliptical waveguide)

Immersion Depth Immersion at specified depth for 24 hours





NEX10 Male for 1/4 in foam coaxial cable, factory attached

Product Classification

Product TypeWireless and radiating connector

Product Brand HELIAX®

General Specifications

Body Style Straight

Inner Contact Attachment Method Solder

Inner Contact Plating Silver

Interface NEX10 Male

Outer Contact Attachment MethodSolderOuter Contact PlatingSilver

Dimensions


Length 25.4 mm | 1 in

Diameter 11.94 mm | 0.47 in

Nominal Size 1/4 in

Outline Drawing





Electrical Specifications

3rd Order IMD at Frequency -119 dBm @ 910 MHz

3rd Order IMD Test Method Two +43 dBm carriers

Insertion Loss Coefficient, typical 0.05

Cable Impedance 50 ohm

Connector Impedance 50 ohm

dc Test Voltage **Inner Contact Resistance, maximum** 2 m0hm

5000 MOhm Insulation Resistance, minimum

0 - 20 GHz **Operating Frequency Band**

Outer Contact Resistance, maximum 1 m0hm

Peak Power, maximum 5 kW

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
0-3000 MHz	1.032	36.06

3000-4000 MHz 1.046 32.96



1500 V

4000–6000 MHz 1.135 23.98 **6000–10000 MHz** 1.135 23.98

Mechanical Specifications

Connector Retention Tensile Force449.27 N | 101 lbfConnector Retention Torque1.1 N-m | 9.736 in lbCoupling Nut Proof Torque5 N-m | 44.254 in lbCoupling Nut Retention Force499.98 N | 112.4 lbf

Interface Durability 100 cycles

Mechanical Shock Test Method IEC 60068-2-27

Environmental Specifications

Operating Temperature $-55 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-67 $^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)Storage Temperature $-65 \,^{\circ}\text{C}$ to $+125 \,^{\circ}\text{C}$ (-85 $^{\circ}\text{F}$ to $+257 \,^{\circ}\text{F}$)

Attenuation, Ambient Temperature20 °C | 68 °FAverage Power, Ambient Temperature40 °C | 104 °FAverage Power, Inner Conductor Temperature100 °C | 212 °FCorrosion Test MethodIEC 60068-2-11

Immersion Depth1 mImmersion Test MatingMated

Immersion Test Method IEC 60529:2001, IP68

Moisture Resistance Test Method IEC 60068-2-3

Thermal Shock Test Method IEC 60068-2-14

Vibration Test Method IEC 60068-2-6

Packaging and Weights

Weight, net 8.8 g | 0.019 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant



UK-ROHS

Compliant



* Footnotes

Insertion Loss Coefficient, typical 0.05√ freq (GHz) (not applicable for elliptical waveguide)

Immersion Depth Immersion at specified depth for 24 hours





FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket

Product Classification

 Product Type
 Coaxial wireless cable

 Product Brand
 HELIAX® | SureFlex®

 Product Series
 FSJ1-50A | MLOC

General Specifications

Flexibility Superflexible

Jacket Color Black

Performance NoteAttenuation values typical, guaranteed within 5%

Dimensions

 Diameter Over Dielectric
 4.826 mm | 0.19 in

 Diameter Over Jacket
 7.366 mm | 0.29 in

 Inner Conductor OD
 1.905 mm | 0.075 in

 Outer Conductor OD
 6.35 mm | 0.25 in

Nominal Size 1/4 in

Electrical Specifications

Cable Impedance50 ohm ±1 ohm

Capacitance 79.4 pF/m | 24.201 pF/ft

dc Resistance, Inner Conductor 9.843 ohms/km | 3 ohms/kft

dc Resistance, Outer Conductor 7.216 ohms/km | 2.199 ohms/kft

dc Test Voltage 1600 V

Inductance 0.2 μ H/m | 0.061 μ H/ft

Insulation Resistance 100000 MOhms-km

Jacket Spark Test Voltage (rms) 5000 V

Operating Frequency Band 1 – 18000 MHz

COMMSCOPE®

Peak Power 6.4 kW
Velocity 82 %

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
680-960 MHz	1.201	20.8
1700-2200 MHz	1.201	20.8
2200-2700 MHz	1.433	15

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Average Power (kW)
1.0	0.577	0.176	6.4
1.5	0.707	0.215	6.4
2.0	0.816	0.249	6.4
10.0	1.833	0.559	3.99
20.0	2.6	0.792	2.81
30.0	3.192	0.973	2.29
50.0	4.136	1.261	1.77
85.0	5.419	1.652	1.35
88.0	5.516	1.681	1.33
100.0	5.889	1.795	1.24
108.0	6.125	1.867	1.19
150.0	7.25	2.21	1.01
174.0	7.825	2.385	0.93
200.0	8.408	2.563	0.87
204.0	8.495	2.589	0.86
300.0	10.373	3.162	0.71
400.0	12.051	3.673	0.61
450.0	12.817	3.906	0.57
460.0	12.965	3.952	0.56
500.0	13.545	4.128	0.54
512.0	13.715	4.18	0.53
600.0	14.909	4.544	0.49
700.0	16.175	4.93	0.45
800.0	17.362	5.292	0.42

Page 12 of 15



824.0	17.637	5.376	0.41
894.0	18.42	5.614	0.4
960.0	19.134	5.832	0.38
1000.0	19.556	5.96	0.37
1218.0	21.738	6.626	0.34
1250.0	22.044	6.719	0.33
1500.0	24.326	7.414	0.3
1700.0	26.038	7.936	0.28
1794.0	26.813	8.172	0.27
1800.0	26.862	8.187	0.27
2000.0	28.455	8.673	0.26
2100.0	29.227	8.908	0.25
2200.0	29.984	9.139	0.24
2300.0	30.727	9.365	0.24
2500.0	32.174	9.806	0.23
2700.0	33.576	10.233	0.22
3000.0	35.602	10.851	0.21
3400.0	38.183	11.638	0.19
3600.0	39.428	12.017	0.19
3700.0	40.041	12.204	0.18
3800.0	40.647	12.389	0.18
3900.0	41.247	12.571	0.18
4000.0	41.841	12.753	0.17
4100.0	42.429	12.932	0.17
4200.0	43.012	13.11	0.17
4300.0	43.59	13.286	0.17
4400.0	44.163	13.46	0.17
4500.0	44.73	13.633	0.16
4600.0	45.293	13.805	0.16
4700.0	45.852	13.975	0.16
4800.0	46.405	14.144	0.16
4900.0	46.955	14.311	0.16
5000.0	47.5	14.477	0.15
6000.0	52.747	16.077	0.14
8000.0	62.37	19.01	0.12

Page 13 of 15

8800.0	65.974	20.108	0.11
10000.0	71.173	21.693	0.1
12000.0	79.393	24.198	0.09
14000.0	87.172	26.569	0.08
15800.0	93.872	28.611	0.08
16000.0	94.601	28.833	0.08
18000.0	101.745	31.01	0.07

Material Specifications

Dielectric Material Foam PE

Jacket Material PE

Inner Conductor Material Copper-clad aluminum wire

Outer Conductor Material Corrugated copper

Mechanical Specifications

Minimum Bend Radius, multiple Bends25.4 mm | 1 inMinimum Bend Radius, single Bend25.4 mm | 1 in

Number of Bends, minimum 15 Number of Bends, typical 20

 Tensile Strength
 68 kg | 149.914 lb

 Bending Moment
 0.7 N-m | 6.196 in lb

Flat Plate Crush Strength 1.8 kg/mm | 100.795 lb/in

Environmental Specifications

Installation temperature $-40 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)Operating Temperature $-55 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ ($-67 \,^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)Storage Temperature $-70 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ ($-94 \,^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Attenuation, Ambient Temperature68 °F | 20 °CAverage Power, Ambient Temperature104 °F | 40 °CAverage Power, Inner Conductor Temperature212 °F | 100 °C

Packaging and Weights

Cable weight 0.07 kg/m | 0.047 lb/ft

COMMSCOPE®

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant
UK-ROHS Compliant
UL/ETL Certification Compliant





