FSJ1-50A SureFlex® Jumper with interface types NEX10 Male and 4.3-10 Male Right angle, 2ft

• WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

IP

Product Type		SureFlex® Premium, static PIM
Product Brand		HELIAX® SureFlex®
Product Series		FSJ1-50A
General Specifications		
Body Style, Connector A		Straight
Body Style, Connector B		Right angle
Interface, Connector A		NEX10 Male
Interface, Connector B		4.3-10 Male
Specification Sheet Revision Level		A
Dimensions		
Length		0.61 m 2.001 ft
Nominal Size		1/4 in
Electrical Specifications		
3rd Order IMD		-112 dBm
3rd Order IMD Test Method		Two +43 dBm carriers
VSWR/Return Loss		
Frequency Band	VSWR	Return Loss (

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.065	30.04
1700–2200 MHz	1.083	27.99
2500-2700 MHz	1.106	25.96
3400-3800 MHz	1.222	20.01

Page 1 of 11



F1A-XMHR-2-P

Jumper Assembly Sample Label



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

Included Products

F1XM-P-HS FSJ1-50A NEX10 Male for 1/4 in foam coaxial cable, factory attached

 FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket

Page 2 of 11



F1XM-P-HS



Product Classification


NEX10 Male for 1/4 in foam coaxial cable, factory attached

PIUUULI LIASSIIILALIUII	
Product Type	Wireless and radiating connector
Product Brand	HELIAX®
General Specifications	
Body Style	Straight
Inner Contact Attachment Method	Solder
Inner Contact Plating	Silver
Interface	NEX10 Male
Outer Contact Attachment Method	Solder
Outer Contact Plating	Silver
Dimensions	
Length	25.4 mm 1 in
Diameter	11.94 mm 0.47 in
Nominal Size	1/4 in

Outline Drawing

Page 3 of 11





Electrical Specifications

3rd Order IMD at Frequency	-119 dBm @ 910 MHz
3rd Order IMD Test Method	Two +43 dBm carriers
Insertion Loss Coefficient, typical	0.05
Cable Impedance	50 ohm
Connector Impedance	50 ohm
dc Test Voltage	1500 V
Inner Contact Resistance, maximum	2 m0hm
Insulation Resistance, minimum	5000 MOhm
Operating Frequency Band	0 – 20 GHz
Outer Contact Resistance, maximum	1 m0hm
Peak Power, maximum	5 kW

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
0–3000 MHz	1.032	36.06
3000–4000 MHz	1.046	32.96

Page 4 of 11



F1XM-P-HS

4000–6000 MHz	1.135	23.98
6000–10000 MHz	1.135	23.98

Mechanical Specifications

Connector Retention Tensile Force	449.27 N 101 lbf
Connector Retention Torque	1.1 N-m 9.736 in lb
Coupling Nut Proof Torque	5 N-m 44.254 in lb
Coupling Nut Retention Force	499.98 N 112.4 lbf
Interface Durability	100 cycles
Mechanical Shock Test Method	IEC 60068-2-27

Environmental Specifications

Operating Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Storage Temperature	-65 °C to +125 °C (-85 °F to +257 °F)
Attenuation, Ambient Temperature	20 °C 68 °F
Average Power, Ambient Temperature	40 °C 104 °F
Average Power, Inner Conductor Temperature	100 °C 212 °F
Corrosion Test Method	IEC 60068-2-11
Immersion Depth	1 m
Immersion Test Mating	Mated
Immersion Test Method	IEC 60529:2001, IP68
Moisture Resistance Test Method	IEC 60068-2-3
Thermal Shock Test Method	IEC 60068-2-14
Vibration Test Method	IEC 60068-2-6

Packaging and Weights

Weight, net

8.8 g | 0.019 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

Page 5 of 11



F1XM-P-HS



Compliant

* Footnotes

Insertion Loss Coefficient, typical 0.05√⁻freq (GHz) (not applicable for elliptical waveguide)

Immersion Depth

Immersion at specified depth for 24 hours

Page 6 of 11



FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket

Coaxial wireless cable

FSJ1-50A | MLOC

4.826 mm | 0.19 in

7.366 mm | 0.29 in

1.905 mm | 0.075 in

6.35 mm | 0.25 in

1/4 in

HELIAX® | SureFlex®

Product Classification

Product Type Product Brand Product Series

General Specifications

 Flexibility
 Superflexible

 Jacket Color
 Black

 Performance Note
 Attenuation values typical, guaranteed within 5%

Dimensions

Diameter Over Dielectric Diameter Over Jacket Inner Conductor OD Outer Conductor OD Nominal Size

Electrical Specifications

Cable Impedance	50 ohm ±1 ohm	
Capacitance	79.4 pF/m 24.201 pF/ft	
dc Resistance, Inner Conductor	9.843 ohms/km 3 ohms/kft	
dc Resistance, Outer Conductor	7.216 ohms/km 2.199 ohms/kft	
dc Test Voltage	1600 V	
Inductance	0.2 µH/m 0.061 µH/ft	
Insulation Resistance	100000 MOhms-km	

Page 7 of 11



Jacket Spark Test Voltage (rms)	5000 V
Operating Frequency Band	1 – 18000 MHz
Peak Power	6.4 kW
Velocity	82 %

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
680–960 MHz	1.201	20.8
1700–2200 MHz	1.201	20.8
2200–2700 MHz	1.433	15

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Average Power (kW)
1.0	0.577	0.176	6.4
1.5	0.707	0.215	6.4
2.0	0.816	0.249	6.4
10.0	1.833	0.559	3.99
20.0	2.6	0.792	2.81
30.0	3.192	0.973	2.29
50.0	4.136	1.261	1.77
85.0	5.419	1.652	1.35
88.0	5.516	1.681	1.33
100.0	5.889	1.795	1.24
108.0	6.125	1.867	1.19
150.0	7.25	2.21	1.01
174.0	7.825	2.385	0.93
200.0	8.408	2.563	0.87
204.0	8.495	2.589	0.86
300.0	10.373	3.162	0.71
400.0	12.051	3.673	0.61
450.0	12.817	3.906	0.57
460.0	12.965	3.952	0.56
500.0	13.545	4.128	0.54
512.0	13.715	4.18	0.53
600.0	14.909	4.544	0.49

Page 8 of 11



700.0	16.175	4.93	0.45
800.0	17.362	5.292	0.42
824.0	17.637	5.376	0.41
894.0	18.42	5.614	0.4
960.0	19.134	5.832	0.38
1000.0	19.556	5.96	0.37
1218.0	21.738	6.626	0.34
1250.0	22.044	6.719	0.33
1500.0	24.326	7.414	0.3
1700.0	26.038	7.936	0.28
1794.0	26.813	8.172	0.27
1800.0	26.862	8.187	0.27
2000.0	28.455	8.673	0.26
2100.0	29.227	8.908	0.25
2200.0	29.984	9.139	0.24
2300.0	30.727	9.365	0.24
2500.0	32.174	9.806	0.23
2700.0	33.576	10.233	0.22
3000.0	35.602	10.851	0.21
3400.0	38.183	11.638	0.19
3600.0	39.428	12.017	0.19
3700.0	40.041	12.204	0.18
3800.0	40.647	12.389	0.18
3900.0	41.247	12.571	0.18
4000.0	41.841	12.753	0.17
4100.0	42.429	12.932	0.17
4200.0	43.012	13.11	0.17
4300.0	43.59	13.286	0.17
4400.0	44.163	13.46	0.17
4500.0	44.73	13.633	0.16
4600.0	45.293	13.805	0.16
4700.0	45.852	13.975	0.16
4800.0	46.405	14.144	0.16
4900.0	46.955	14.311	0.16
5000.0	47.5	14.477	0.15

Page 9 of 11

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 20, 2023

COMMSCOPE®

6000.0	52.747	16.077	0.14
8000.0	62.37	19.01	0.12
8800.0	65.974	20.108	0.11
10000.0	71.173	21.693	0.1
12000.0	79.393	24.198	0.09
14000.0	87.172	26.569	0.08
15800.0	93.872	28.611	0.08
16000.0	94.601	28.833	0.08
18000.0	101.745	31.01	0.07

Material Specifications

Dielectric Material	Foam PE
Jacket Material	PE
Inner Conductor Material	Copper-clad aluminum wire
Outer Conductor Material	Corrugated copper

Mechanical Specifications

Minimum Bend Radius, multiple Bends	25.4 mm 1 in
Minimum Bend Radius, single Bend	25.4 mm 1 in
Number of Bends, minimum	15
Number of Bends, typical	20
Tensile Strength	68 kg 149.914 lb
Bending Moment	0.7 N-m 6.196 in lb
Flat Plate Crush Strength	1.8 kg/mm 100.795 lb/in

Environmental Specifications

Operating Temperature-55 °C to +85 °C (-67 °F to +185 °F)Storage Temperature-70 °C to +85 °C (-94 °F to +185 °F)Attenuation, Ambient Temperature68 °F 20 °CAverage Power, Ambient Temperature104 °F 40 °CAverage Power, Inner Conductor Temperature212 °F 100 °C	Installation temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Attenuation, Ambient Temperature68 °F 20 °CAverage Power, Ambient Temperature104 °F 40 °C	Operating Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Average Power, Ambient Temperature 104 °F 40 °C	Storage Temperature	-70 °C to +85 °C (-94 °F to +185 °F)
	Attenuation, Ambient Temperature	68 °F 20 °C
Average Power, Inner Conductor Temperature212 °F 100 °C	Average Power, Ambient Temperature	104 °F 40 °C
	Average Power, Inner Conductor Temperature	212 °F 100 °C

Packaging and Weights

Page 10 of 11



Cable weight

0.07 kg/m | 0.047 lb/ft

Regulatory Compliance/Certifications

Agency

ROHS

UK-ROHS

UL/ETL Certification

Classification

CHINA-ROHS ISO 9001:2015 Above maximum concentration value Designed, manufactured and/or distributed under this quality management system Compliant Compliant



