# 760255324 | C-012-DN-8M-M12BK/20G/09G-IN00



G652.D compliant fiber drop cable for Indoor/Outdoor use, Gel-filled loose tube, 12 fiber, Meter jacket marking, Black

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | China | India

Portfolio CommScope®

Product Type Fiber indoor/outdoor cable

**Product Series** C-DN

### General Specifications

Cable Type Central loose tube

Construction Type Non-armored

Subunit Type Gel-filled

Jacket Color Black

Jacket Marking Meters

Subunit, quantity 1

Fibers per Subunit, quantity 12

Total Fiber Count 12

#### **Dimensions**


**Buffer Tube/Subunit Diameter** 2 mm | 0.079 in

**Diameter Over Jacket** 5.05 mm | 0.199 in

## Representative Image



# 760255324 | C-012-DN-8M-M12BK/20G/09G-IN00



## Mechanical Specifications

Minimum Bend Radius, loaded50 mm1 .969 inMinimum Bend Radius, storage coils50 mm1 .969 in

Minimum Bend Radius, unloaded50 mm | 1.969 inTensile Load, long term, maximum400 N | 89.924 lbfTensile Load, short term, maximum1500 N | 337.214 lbf

Tensile Load, short term, maximum 1500 N | 337.214 lbf

Cable Crush Resistance, maximum 15 N/mm | 85.652 lb/in

**Compression** 15 N/mm | 85.652 lb/in

**Compression Test Method** IEC 60794-1-2 E3

**Impact** 3 N-m | 26.552 in lb

Impact Test Method IEC 60794-1 E4

**Strain** 0.60%

Strain Test Method IEC 60794-1 E1

Twist 5 cycles

Twist Test Method IEC 60794-1 E7

**Optical Specifications** 

**Fiber Type** G.652.D

Optical Specifications, Wavelength Specific

 $\textbf{Attenuation, maximum} \hspace{1.5cm} 0.30 \hspace{1mm} \text{dB/km} \hspace{1mm} \textcircled{@ 1,550} \hspace{1mm} \textbf{l} \hspace{1mm} 0.40 \hspace{1mm} \text{dB/km} \hspace{1mm} \textcircled{@ 1,310} \hspace{1mm} \textbf{nm}$ 

**Environmental Specifications** 



# 760255324 | C-012-DN-8M-M12BK/20G/09G-

Installation temperature  $-15 \,^{\circ}\text{C}$  to  $+40 \,^{\circ}\text{C}$  ( $+5 \,^{\circ}\text{F}$  to  $+104 \,^{\circ}\text{F}$ )

Operating Temperature  $-25 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  ( $-13 \,^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

**Storage Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

Cable Qualification Standards IEC 60794-1-2

Environmental Space Drop | Universal Low Smoke Zero Halogen (ULSZH)

Water Penetration 24 h

**Environmental Test Specifications** 

**Temperature Cycle**  $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

**Temperature Cycle Test Method** IEC 60794-1-2 F1

Packaging and Weights

Cable weight 30 kg/km | 20.159 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



#### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

