# 760256107 | P-192-MZ-5G-F12LM/20T



Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, interlocking aluminum armored with plenum jacket, Multimode OM5, 192 fiber multiunit with 12 fiber subunits, gel-free, Feet jacket marking, Lime-green jacket color

#### Product Classification

Regional Availability	Asia   Australia/New Zealand   Latin America   Middle East /Africa   North America	
Portfolio	CommScope®	
Product Type	Fiber indoor cable	
Product Series	P-MZ	
General Specifications		
Armor Type	Interlocking aluminum	
Cable Type	MPO trunk cable	
Construction Type	Armored	
Subunit Type	Gel-free	
Filler, quantity	2	
Jacket Color	Lime green	
Jacket Marking	Feet	
Subunit, quantity	16	
Fibers per Subunit, quantity	12	
Total Fiber Count	192	
Dimensions		
Buffer Tube/Subunit Diameter	2 mm   0.079 in	
Diameter Over Armor	18.4 mm   0.724 in	
Diameter Over Jacket	20.5 mm   0.807 in	

### Representative Image

Page 1 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 21, 2025



# 760256107 | P-192-MZ-5G-F12LM/20T



#### Mechanical Specifications

Minimum Bend Radius, loaded	307 mm   12.087 in
Minimum Bend Radius, unloaded	205 mm   8.071 in
Tensile Load, long term, maximum	200 N   44.962 lbf
Tensile Load, short term, maximum	667 N   149.948 lbf
Compression	85 N/mm   485.363 lb/in
Compression Test Method	FOTP-41   IEC 60794-1 E3
Flex	25 cycles
Flex Test Method	FOTP-104   IEC 60794-1 E6
Impact	35 N-m   309.776 in lb
Impact Test Method	FOTP-25   IEC 60794-1 E4
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33   IEC 60794-1 E1
Twist	10 cycles
Twist Test Method	FOTP-85   IEC 60794-1 E7
Vertical Rise, maximum	45 m   147.638 ft
Optical Specifications	
Fiber Type	OM5, LazrSPEED® wideband

### Environmental Specifications

Installation temperature

0 °C to +70 °C (+32 °F to +158 °F)

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 21, 2025



# 760256107 | P-192-MZ-5G-F12LM/20T

Operating Temperature	0 °C to +70 °C (+32 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Cable Qualification Standards	ANSI/ICEA S-83-596   Telcordia GR-409
Environmental Space	Plenum
Flame Test Listing	NEC OFCP (ETL) and c(ETL)
Flame Test Method	NFPA 130   NFPA 262

### **Environmental Test Specifications**

Heat Age	0 °C to +85 °C (+32 °F to +185 °F)
Heat Age Test Method	IEC 60794-1 F9
Low High Bend	0 °C to +70 °C (+32 °F to +158 °F)
Low High Bend Test Method	FOTP-37   IEC 60794-1 E11
Temperature Cycle	0 °C to +70 °C (+32 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3   IEC 60794-1 F1

### Packaging and Weights

375 kg/km | 251.988 lb/kft

#### Included Products

CS-5K-MP

 LazrSPEED® 550 OM4 Bend-Insensitive Multimode Fiber

### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

Page 3 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 21, 2025

